

TRI-ONIC®

# TRM

## 1-1/2" X 13/32" MIDGET FUSES



Tri-onic TRM time-delay midget fuses are rated 250 volts AC and are offered in ampere ratings from 1/10A to 30A. They have 12 seconds time delay at 200% rating to provide supplemental protection of small motors, small transformers and other high inrush loads, plus many other 250 volt applications. (Not for Branch Circuit Protection).

### Features/Benefits

- **Numerous ratings** for a wide variety of applications
- **250VAC rating** in all sizes up to 30A
- **Time delay** for circuits with high inrush current
- Can be used with **ULTRASAFE™** fuse holders

### HIGHLIGHTS:

- Time Delay
- 250 VAC Rated

### APPLICATIONS:

- Small Motors
- Small Transformers
- Lighting Circuits
- Control Circuits

### Ratings

- **AC:** 1/10 to 30A  
250VAC, 10kA I.R.

### Approvals

- UL Listed to Standard 248-14 File E33925
- CSA Certified to Standard C22.2 No. 248.14




C

### Standard Fuse Ampere Ratings, Catalog Numbers

AMPERE RATING	CATALOG NUMBER	AMPERE RATING	CATALOG NUMBER	AMPERE RATING	CATALOG NUMBER	AMPERE RATING	CATALOG NUMBER	AMPERE RATING	CATALOG NUMBER	AMPERE RATING	CATALOG NUMBER
1/10	TRM1/10	6/10	TRM6/10	1-6/10	TRM1-6/10	3	TRM3	5-6/10	TRM5-6/10	10	TRM10
15/100	TRM15/100	8/10	TRM8/10	1-8/10	TRM1-8/10	3-2/10	TRM3-2/10	6	TRM6	12	TRM12
2/10	TRM2/10	1	TRM1	2	TRM2	3-1/2	TRM3-1/2	6-1/4	TRM6-1/4	15	TRM15
1/4	TRM1/4	1-1/8	TRM1-1/8	2-1/4	TRM2-1/4	4	TRM4	7	TRM7	20	TRM20
3/10	TRM3/10	1-1/4	TRM1-1/4	2-1/2	TRM2-1/2	4-1/2	TRM4-1/2	8	TRM8	25	TRM25
4/10	TRM4/10	1-4/10	TRM1-4/10	2-8/10	TRM2-8/10	5	TRM5	9	TRM9	30	TRM30
1/2	TRM1/2										

### Melting Time – Current Data 1/10 - 3-1/2 Amperes, 250 Volts AC



### Melting Time – Current Data 4 - 30 Amperes, 250 Volts AC

