


5262



Flush, nylon face, back and side wired, multiple drive screws.

Hubbell Wiring Device-Kellems Product Specifications

Device Type	Flush Receptacle
Receptacle Style	Duplex
Face Shape	Standard
Standard	NEMA
Amperage	15A
Voltage	125V
Poles and Wires	2 Pole, 3 Wire Grounding
Wiring Method	Back and Side
Hospital Grade ?	No
Receptacle Grade	Heavy Duty Spec Grade
Face Style	Finder Groove
Color	 Brown
NEMA No.	5-15R
Horsepower	0.5
Description	Heavy Duty Straight Blade Duplex Receptacle
Type	2 Pole, 3 Wire, Grounding
Rating	15A, 125V
Certification	-UL Listed to UL498 File E2186, Guide RTRT Fed Spec WC596G, Meets WD-1 Heavy Duty and WD-6 requirements, Certified to CSA, C22.2, No. 42 file 285.
Terminal Screw	#10-32 Silicon Bronze (Ni plate if neutral)

Material	
Ground Screw Material	#10-32 Silicon Bronze (Green)
Wire Clamps Material	.031" (.8) Brass
Top Material	Nylon
Base Material	Reinforced PET
Power Contacts Material	.037" (.9) Brass
Mounting Strap Material	.050" (1.3) Brass
Center Assembly Rivet Material	Brass
Auto Ground Clip Material	Stainless Steel
Mounting Screw Material	Steel-Zinc Plated
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 V2 or better
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).

