

Product Details and Certifications

Cross Reference RA Part Number: 700-CF220A A

Product: 700-CF220A

Description: MCS-CF Control Relay, 2 N.O. / 2 N.C., 240V 60Hz



Representative Photo Only (actual product may vary based on configuration selections)

CONTROL RELAY DATA

Relay Coil Voltage	4-Pole AC Coil Voltage
Terminal Type	Screw Terminals
Contact Type	Standard Contacts
Contact Configuration	2 N.O. - 2 N.C.
Control Voltage	240V 60 Hz

CERTIFICATIONS AND APPROVALS

cULus
CE
CSA

RECOMMENDED SPARE PARTS

TA474	220V 50Hz / 240V 60Hz Coil
-------	----------------------------



Bulletin 700-CF — Control Relay

- IEC industrial relays
- Mechanically linked contact performance per IEC 60947-5-1
- Gold plated, bifurcated version for low level switching applications
- Master control relay version rated 15 A (AC-15)
- Solid-state and pneumatic timing modules
- 4-...10 Poles

Certifications

cULus Listed (File No. E14840, Guide NKCR/NKCR7)
CE Marked
CCC Certified

Table of Contents

Product Selection this page
Accessories..... 9-150
Specifications..... 9-154
Approximate Dimensions..... 9-156
Standards Compliance
UL 508
CSA C22.2 No. 14
EN/IEC 60947-1, -5-1
Meets the material restrictions for European Directive 2002/95/EC - EU-RoHS

4-Pole AC Coil Voltage (Ratings for 700-CF Only)

AC-12		AC-15							Connection Diagrams	Contacts		Standard Contacts Cat. No.*	Gold Plated Bifurcated Contacts Cat. No.*	Master Contacts Cat. No.*
I_{th} [A]		I_e [A]								N.O.	N.C.			
40 °C	60 °C	24/48V	120V	240V	400V	500V	600V	690V						
20	20	10	10	10	6	2.5	1	1		2	2	700-CF220*	700-CFB220*	700-CFM220*
										3	1	700-CF310*	700-CFB310*	700-CFM310*
										4	0	700-CF400*	700-CFB400*	700-CFM400*
										0	4	700-CF040*	700-CFB040*	—

* For spring clamp terminals, insert **R** after 700-C. Example: **Cat. No. 700-CRF220D**.

⊗ AC Coil Voltage Code

The cat. no. as listed is incomplete. Select a coil voltage code from the table below to complete the cat. no. Example: **Cat. No. 700-CF220*** becomes **Cat. No. 700-CF220D** for 120V, 60 Hz

[V]	12	24	32	36	42	48	100	110	120	127	200	220	208	220	230	240	277	347	380	380	400	400	415	440	480	500	550	600
50 Hz	R	K	V	W	X	Y	KP	—	D	P	S	KG	L	—	F	—	VA	T	—	—	N	—	G	B	—	M	C	—
60 Hz	Q	J	—	V	—	X	—	KP	—	D	—	—	KG	H	L	—	—	—	—	—	—	—	—	N	B	—	—	C
50/60 Hz	—	KJ	—	—	—	KY	KP	—	KD	—	—	KG	KL	—	KL	KF	—	KA	—	—	—	—	KN	—	KB	—	—	—

4-Pole DC Coil Voltage (Ratings for 700-CF Only)

AC-12		AC-15							Connection Diagrams	Contacts		Standard Contacts Cat. No.‡	Gold Plated Bifurcated Contacts Cat. No.*	Master Contacts Cat. No.*
I_{th} [A]		I_e [A]								N.O.	N.C.			
40 °C	60 °C	24/48V	120V	240V	400V	500V	600V	690V						
20	20	10	10	10	6	2.5	1	1		2	2	700-CF220*	700-CFB220*	700-CFM220*
										3	1	700-CF310*	700-CFB310*	700-CFM310*
										4	0	700-CF400*	700-CFB400*	700-CFM400*

‡ For spring clamp terminals, insert **R** after 700-C. Example: **Cat. No. 700-CRF220ZJ**.

* Ratings for Bulletin 700-CFB and 700-CFM are on page 9-159

⊗ DC Coil Voltage Code§

The cat. no. as listed is incomplete. Select a coil voltage code from the table below to complete the cat. no. example: **Cat. No. 700-CF220*** becomes **Cat. No. 700-CF220ZJ** for 24V DC

[V]	9	12	24	36	48	48... 72	60	64	72	80	110	110... 125	115	125	220	220... 250	230	250
Standard	ZR	ZQ	ZJ	ZW	ZY	—	ZZ	ZB	ZG	ZE	ZD	—	ZP	ZS	ZA	—	ZF	ZT
Standard diode	—	—	DJ	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—
Electronic with diode	—	EQ	EJ	—	—	EY	—	—	—	—	—	ED	—	—	—	EA	—	—

§ When ordering DJ coil with built-in surge suppression, the DJ is not polarity sensitive. Drop out time: 14...20 ms.

Control Circuit

Cat. No. 700-CF			
Operating Voltage			
AC 50/60 Hz	Pickup	[x U _s]	0.85...1.1
	Dropout	[x U _s]	0.3...0.6
DC*	Pickup	[x U _s]	0.8...1.1
	Dropout	[x U _s]	0.1...0.6
Coil Consumption			
AC 50/60 Hz	Inrush	[VA/W]	70/50
	Seal	[VA/W]	8/2.6
DC (conventional)	Inrush/Seal	[W]	6.5
DC (electronic)	Inrush (avg./peak)	[W]	10/17
	Seal	[W]	1.7
Operating Times			
AC 50/60 Hz	Pickup Time	[ms]	15...30
	Dropout Time	[ms]	10...60
DC (conventional)	Pickup Time	[ms]	40...70
	Dropout Time	[ms]	7...15
DC (electronic)	Pickup Time	[ms]	25...50
	Dropout Time	[ms]	25...50
Min OFF time		[ms]	200
Max. ripple			± 15%
Latch Attachment Release, 100-FL			
Coil Consumption	AC	[VA/W]	45/40
	DC	[W]	25
Contact Signal Duration		[min./max]	0.03...15 s
Timing Attachment			
Reset Time, 100-ETA, 100-ETB	at min. time setting	[ms]	10
	at max. time setting	[ms]	70
Repeat Accuracy			± 10%

* For 9V DC, code ZR, use operating voltage 0.65...1.3 x U_s.
For 24V DC, code ZJ, DJ, or EJ use operating voltage 0.7...1.25 x U_s.
For 110V DC, code ED use operating voltage 0.7...1.25 x U_s.

General

Cat. No. 700-CF	
Rated Insulation Voltage U_i	
IEC	690V
UL; CSA	600V
Rated Impulse Strength U_{imp}	
6 kV	
High Test Voltage 1 minute (per IEC 60947-4)	
2500V	
Rated Voltage U_e	
AC	115, 230, 400, 500, 690V
DC	24, 48, 110, 220, 440V
Short-Circuit Protection gG Fuse 10 A	
Rated Frequency	
50/60 Hz, DC	
Ambient Temperature	
Storage	-55...+80 °C (-67...176 °F)
Operation at nominal current	-25...+60 °C (-13...140 °F)
15% current reduction for AC-12 at > 60 °C	-25...+70 °C (-13...158 °F)
Corrosion Resistance	
humid-alternating climate, cyclic, per IEC 60068-2-30 and DIN 50 016, 56 cycles	
Altitude	
2000 m above mean sea level, per IEC60 947-4	
Type of Protection	
IP2X (IEC 60529 and DIN 40050)	in connected state
Shock Resistance	IEC 60068-2: Half sinusoidal shock 11 ms, 30 G (in 3 directions)
Vibration Resistance	IEC 60068-2: Static >2 G, in normal position no malfunction <5 G

Utilization Category Table from EN 60947-5-1

Verification of Making and Breaking Capacities of Switching Elements Under Normal Conditions
Corresponding to the Utilization Categories*

Utilization Category	Normal Condition of Use								
	Make‡			Break‡			Number and Rate of Making and Breaking operations		
	I/I _e	U/U _e	cos ψ	I/I _e	U/U _e	cos ψ	No. operating cycles§	Operating cycles per minute	ON time [s]➤
AC-12⌘	1	1	0.9	1	1	0.9	6050	6	0.05
AC-13⌘	2	1	0.65	1	1	0.65	6050	6	0.05
AC-14⌘	6	1	0.3	1	1	0.3	6050	6	0.05
AC-15⌘	10	1	0.3	1	1	0.3	6050	6	0.05
DC	—	—	T _{0.95}	—	—	T _{0.95}	—	—	—
DC-12	1	1	1 ms	1	1	1 ms	6050	6	0.05➤
DC-13	1	1	6 x P*	1	1	6 x P*	6050	6	0.05➤
DC-14⌘	10	1	15 ms	1	1	15 ms	6050	—	0.05➤

I_e Rated operational current, I Current to be made or broken

U_e Rated operational voltage, U Voltage before make

PU_eI_e Steady-state power consumption (W)

T_{0.95} Time to reach 95% of the steady-state current (ms)

* See sub-clause 8.3.3.5.2.

‡ For tolerances on test quantities, see sub-clause 8.3.2.2.

§ The first 50 operating cycles shall be run at U/U_e=1.1 with the loads set at U_e.

♣ The value "6 x P" results from an empirical relationship which is found to represent most DC magnetic loads to an upper limit of P = 50 W, e.g., 6 x P= 300 W.

➤ The ON time shall be at least equal to T_{0.95}.

⌘ Where the break current differs from the make current value, the ON time refers to the make current value after which the current is reduced to the break current value for a suitable period e.g., 0.05 s.