


GENERAL NOTES:

- 1) FLAT BLACK FINISH OVER ENTIRE TRANSFORMER.
- 2) 1/2" MINIMUM SPACING BETWEEN ADJACENT TERMINALS AND BETWEEN TERMINALS AND GROUND MEASURED ON COIL SURFACE.
- 3) IDENTIFY ALL TERMINALS ON SIDE OF COIL.
- 4) NAMEPLATE TO BE OBTAINED FROM ALLEN-BRADLEY CO. OR SUPPLIER. STAMP NAMEPLATE WITH A-B PART NUMBER, PRIMARY AND SECONDARY VOLTAGES, FREQUENCY, AND KVA. UL RECOGNIZED "TYPE" DESIGNATION AND CSA "FILE NUMBER" MUST BE STAMPED BY EACH SUPPLIER ON THE NAMEPLATE. MOUNT NAMEPLATE ON TRANSFORMER TO BE READ FROM THE SECONDARY SIDE, AND CENTER NAMEPLATE ON CORE TO PROVIDE SPACE FOR FUSE LABEL.

REFERENCE		DUAL VOLTAGE CONTROL TRANSFORMER		MAC DOCUMENT	
REVISION AUTHORIZATION		DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED		THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.	
7	2075-96			LOCATION: MILWAUKEE WISCONSIN U.S.A.	
		DR. L.A. MICKELSON	DATE 3-31-97	DWG SIZE	SHEET 1 OF 2
		CHKD. <i>H. Mickelson</i>	DATE 3-31-97	B	X-210922-41
		APPD. <i>Joe L. ...</i>	DATE 3-31-97		



X-210941	P	THIS DWG.	.200	380/220	24	50	4-3/4	2-3/4	1-3/4	3-3/4	3-9/16	H-18969	NONE	
X-210940	P	THIS DWG.	.200	120	32/30/28	60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210939	P	THIS DWG.	.200	400/380	110	50/60	4-3/4	2-3/4	1-3/4	3-3/4	3-9/16	H-18969	NONE	
X-210938	P	THIS DWG.	.200	220/440	60	60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210937	P	THIS DWG.	.200	220/440	32	60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210936	P	THIS DWG.	.200	240/480	32	60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210935	P	THIS DWG.	.200	220/440/550	110	50/60	4-3/4	2-3/4	1-3/4	3-3/4	3-9/16	H-18969	NONE	
X-210934	P	THIS DWG.	.200	110/220	24	60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210933	P	THIS DWG.	.200	220/440	110/100	50/40	4-3/4	2-3/4	1-3/4	3-3/4	3-9/16	H-18969	NONE	100V TAP 200VA
X-210932	P	THIS DWG.	.200	240/480	120/10	50	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	10V TAF 75VA
X-210931	P	THIS DWG.	.100	240/480	120	25	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210930	P	THIS DWG.	.200	380/220	110	50	4-3/4	2-3/4	1-3/4	3-3/4	3-9/16	H-18969	NONE	
X-210929	P	THIS DWG.	.200	220/440	12	60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210928	P	THIS DWG.	.200	220/440/550	24	60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210927	P	THIS DWG.	.200	110	32/30/28	60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210926	P	THIS DWG.	.200	220/440	110/220	50/60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210925	P	THIS DWG.	.100	220/440	110	25	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210924	Q	THIS DWG.	.200	240/480	110	50/60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210923	Q	THIS DWG.	.200	220/440	110/93	50/60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	H-18969	NONE	
X-210922	Q	THIS DWG.	.200	220/440 240/480	110 120	50/60 60	4-5/8	2-5/8	1-5/8	3-5/8	3-7/16	45010-334-05	1497-N5	
PART NO.	CHG. LTR.	MAT	K.V.A.	PRIMARY VOLTAGES	SECOND.	HERTZ	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	DIM. "E"	NAME PLATE	CAT. NO. REF.	REMARKS

REFERENCE		DUAL VOLTAGE CONTROL TRANSFORMER 				MAC DOCUMENT THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.	
REVISION AUTHORIZATION 7 2075-96 DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED xx: ± xxx: ± ANGLES: ±						DR. L.A. MICKELSON DATE 3-31-97 CHKD. _____ DATE _____ APPD. _____ DATE _____	