

# Product Details and Certifications

## Cross Reference RA Part Number: 800T-PH16G T

 **Product: 800T-PH16G**

Description: 30.5mm Type 4/13 Pilot Light, Xfmr, No Test Option, LED, Green, 120V AC 50/60 Hz



Representative Photo Only (actual product may vary based on configuration selections)

### ***PUSH BUTTON DATA***

---

Hazardous Location	Yes
Finger Safe Guards	No Guards
Power Module Type	Transformer
Lamp Test Options	No Test Option
Illumination Options	LED
Voltage	120V AC 50/60 Hz
Lens Color	Green
Contact Blocks	None

### ***ASSEMBLY***

---

Factory or User Assembled?	Factory Assembled
----------------------------	-------------------

### ***CERTIFICATIONS AND APPROVALS***

---

UL	Listed E14840, E10314; Guide #NKCR, NOIV
CSA	LR1234, LR11924, 22.2 #14
CE	60947-5-1
For UL Certifications Directory:	<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>

### ***RECOMMENDED SPARE PARTS***

---

800T-N235	LOCKING RING ①
800T-N293	THRUST WASHER
800T-N292	TRIM WASHER
800T-N19	GASKET

① Locking Ring repair parts are for Series N and later devices. For illuminated selector switches, see footnote 2.

② Locking Ring repair parts are for Series U units only. For Series T units, replace the entire device

# Bulletin 800T/H

## 30.5 mm Push Buttons

### Pilot Lights

#### Pilot Light Devices\*



Transformer Type Pilot Light  
Cat. No. 800T-P16R



Push-to-Test Pilot Light  
Cat. No. 800T-PT16R

Type	Lamp Type	Volts	Color	Type 4/13		Type 4/4X/13	
				Pilot Light	Push-to-Test*	Pilot Light	Push-to-Test*
				Cat. No.	Cat. No.	Cat. No.	Cat. No.
Operator Only*				800T-S00	800T-SB00XX	800H-SR00	800H-SRB00XX
Full Voltage†	Incandescent	24V AC/DC	Red	800T-Q24R	800T-QT24R	800H-QR24R	800H-QRT24R
			Green	800T-Q24G	800T-QT24G	800H-QR24G	800H-QRT24G
			Amber	800T-Q24A	800T-QT24A	800H-QR24A	800H-QRT24A
	No Lamp	0...250V AC/DC	No Lens	800T-QN25	800T-QTN25	—	—
Universal†	LED	12...130 V AC/DC	Red	800T-QH2R	800T-QTH2R	800H-QRH2R	800H-QRTH2R
			Green	800T-QH2G	800T-QTH2G	800H-QRH2G	800H-QRTH2G
			Amber	800T-QH2A	800T-QTH2A	800H-QRH2A	800H-QRTH2A
Transformer‡	Incandescent	120V AC, 50/60 Hz	Red	800T-P16R	800T-PT16R	800H-PR16R	800H-PRT16R
			Green	800T-P16G	800T-PT16G	800H-PR16G	800H-PRT16G
			Amber	800T-P16A	800T-PT16A	800H-PR16A	800H-PRT16A
	Red		800T-PH16R	800T-PTH16R	800H-PRH16R	800H-PRTH16R	
	Green		800T-PH16G	800T-PTH16G	800H-PRH16G	800H-PRTH16G	
	Amber		800T-PH16A	800T-PTH16A	800H-PRH16A	800H-PRTH16A	
	No Lamp		No Lens	800T-PN16	800T-PTN16	—	—


\* Includes one standard Cat. No. 800T-XA (1 N.O. - 1 N.C.) contact block.

\* Operator only supplied without power module, lamp, lens cap, or contact blocks.

† All pilot lights except push-to-test without sealed contacts and dual input transformer relay, are rated for Class 1, Division 2 applications.

800 T - P H 16 G (Push-to-Test)

a b c d e f g h



<b>a</b>		<b>d</b>		<b>f</b>		<b>g</b>		
Protection Rating		Lamp Test Options		Voltage		Lens Color		
Code	Description	Code	Description	Code	Description	Code	Color	Glass Code
T	Metal, Type 4/13	Blank	No test option	16	120V AC 50/60 Hz	Blank	No lens	Blank
H	Plastic, Type 4/4X/13	T	Push-to-test	26	240V AC 50/60 Hz	A	Amber	D
<b>b</b>		<b>e</b>		Full Voltage — Incandescent		B	Blue	E
Finger-Safe Guards		Illumination Options		12 12V AC/DC		C	Clear	F
Code	Description	Code	Description	24 24V AC/DC		G	Green	H
Blank	No guards	Blank	Incandescent	48 48V AC/DC		R	Red	J
C	Guards on terminals	H	LED*	10 120V AC/DC		W	White	K
<b>c</b>		<b>h</b>		20 240V AC/DC		Contact Blocks (Push-to-test units only)		
Power Module Type		Standard		Universal — LED		Code	Description	
800T Type 4/13	Description	800H Type 4/4X/13	Description	2 12...130V AC/DC		Blank	1 N.O. - 1 N.C.	
Code	Description	Code	Description	Dual Input		PenTUFF (Low Voltage)		
P	Transformer (or dual input)	PR	Full voltage/Universal	16 120V AC		AV	1 N.O. - 1 N.C.	
Q	Full voltage/Universal	QR	Full voltage/Universal	24 24V AC/DC (Dual input diode only)		Class 1, Div. 2/Zone 2		
						Logic Reed		
						AR	1 N.O. - 1 N.C.	
						Sealed Switch		
						AP	1 N.O. - 1 N.C.	
						Stackable Sealed Switch		
						AY	1 N.O. - 1 N.C.	

\* LED illumination option is not available with diode type dual input.

‡ Diode type dual input provides circuit isolation via opposing diodes. Not recommended for use with solid-state outputs.

▲ Glass lens available on 800T pilot lights only. Not available on push-to-test units.