



A-B NAMEPLATE (SEE TABLE)
 STAMP NAMEPLATE WITH CATALOG OR PART
 NUMBER, PRIM. & SEC. VOLTAGES AND HERTZ,
 AND KVA AS SHOWN.

ALLEN-BRADLEY NAMEPLATE FURNISHED TO
 SUPPLIER ON REQUEST. NAMEPLATE TO BE
 STAMPED BY SUPPLIER AS DIRECTED AND
 MOUNTED ON THE TRANS. TO READ FROM THE
 SECONDARY SIDE.

1/2" MINIMUM SPACING BETWEEN ADJACENT
 TERM. & BETWEEN TERM. AND GROUND
 MEASURED ON COIL SURFACE.

FLAT BLACK FINISH OVER ENTIRE
 TRANSFORMER.

IDENTIFY ALL TERMINALS ON SIDE OF COIL.

UL RECOGNIZED "TYPE" DESIGNATION AND CSA
 "FILE NUMBER" MUST BE STAMPED BY EACH
 SUPPLIER ON ALLEN-BRADLEY NAMEPLATE.

PART NO.	CHG. LTR.	K.V.A.	PRIM. SEC.		HERTZ	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	NAME PLATE	CAT. NO. REF.	REMARKS
			VOLTAGES	VOLTAGES								
X-231398	D	.750	220	110	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231399	D	.750	440	110	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231400	G	.750	600	120	60	7-1/8		6-1/8	4-3/8	45010-334-24	1497-N35	
X-231401	D	.350	220	110	25	6-7/8		5-7/8	4-1/8	H-18969	NONE	
X-231402	D	.350	440	110	25	6-7/8		5-7/8	4-1/8	H-18969	NONE	OBSELETE
X-231403	D	.350	550	110	25	6-7/8		5-7/8	4-1/8	H-18969	NONE	
X-231404	D	.750	380	110	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231405	D	.550	160	110	42	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231406	D	.750	400	110	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231407	D	.750	550	220	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231408	D	.750	500	220	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231409	D	.750	500	110	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231410	D	.750	440	220	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231411	D	.750	480	220	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231412	D	.750	110	24	60	6-3/4		5-3/4	4	H-18969	NONE	NOTE 1- 10-32 UNF-2B
X-231413	E	.750	208	120	60	6-3/4		5-3/4	4	45010-334-22	1497-N33	
X-231414	E	.750	240	120	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231415	E	.750	480	120	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231416	F	.750	600	120	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231417	H	.750	380	120	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231418	J	.750	415	110	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231419	K	.750	480	240	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231420	E	.750	480	120	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231421	E	.750	240	24	60	6-3/4		5-3/4	4	H-18969	NONE	NOTE 1- 10-32 UNF-2B
X-231422	E	.750	120	120	60	6-3/4		5-3/4	4	H-18969	NONE	

PARTIALLY DISCONTINUED		
DISCONTINUED DATE:		1-83
P.O.N.	ECN	NO.
75-37	7723-76	12
PARTS: X-231402		

REFERENCE REVISION AUTHORIZATION 17 2075-96 DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED XX: ± XXX: ± ANGLES: ±		CONT. XFMR. 0.750 KVA FRAME SIZE EQUIVALENT TO HEVI-DUTY SZ0 CONTROL TRANSFORMER DESIGN 		MAC DOCUMENT THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC. LOCATION: MILWAUKEE, WISCONSIN U.S.A. DR. D. EVANS DATE 7-8-96 DWG SIZE SHEET 1 OF 1 CHKD. <i>H. Mykelsen</i> DATE 3-27-97 APPD. <i>Joe Logigian</i> DATE 3-31-97	
				B X-231398-422	