

Series C Molded Case Circuit Breakers 300 – 800 Amperes

M-Frame

Types MDL and HMDL Electronic Circuit Breakers with Interchangeable Trip Units


Order as Individual Components: Breaker Frame, Trip Unit, Rating Plug, Terminals.

Table 12-236. Types MDL and HMDL Electronic Circuit Breakers with Interchangeable Trip Units

Maximum Continuous Ampere Rating at 40°C ①	Circuit Breaker Frame Only				Digitrip RMS 310 Trip Unit Only ②		Digitrip RMS 310 Rating Plug Only				Terminals
	Standard Interrupting Capacity 600 Vac Rated 50 kAIC at 480 Vac		High Interrupting Capacity 600 Vac Rated 65 kAIC at 480 Vac		L – Adjustable Long Delay Pickup (by Adjustable Rating Plug) S – Adjustable Short Delay Pickup with Fixed Short Delay Time (I ² t Response) or Adjustable Short Delay Time (Flat Response) I – Adjustable Instantaneous Pickup by Setting Short Delay Time to Instantaneous G – Adjustable Ground Fault Pickup with Adjustable Ground Fault Delay (Flat Response)	Ampere Rating	Fixed Rating Plug	Adjustable Rating Plugs			
	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$				Ampere Rating	Catalog Number	Price U.S. \$	

12

3-Pole

800	MDL3800F		HMDL3800F		MES3800LS MES3800LSI MES3800LSG MES3800LSIG —		400 500 600 700 800	8MES400T 8MES500T 8MES600T 8MES700T 8MES800T	 400/500/600/800 A8MES800T 620/640/660/680 A8MES600T5 720/740/760/780 A8MES700T5	See Page 12-140 for Standard and Optional Terminals
-----	----------	--	-----------	--	---	--	---------------------------------	--	--	---

① Ampere rating is established by rating plug.

② For ac use only.