



Class H & K Fuse Holder - 250 Volt

Specifications:

- Have Been Tested & Approved for 10,000 Amp Interrupting Capacity
- Patented Cool Clip® Design
- UL Listed File No. E35113
- CSA Cert. File No. LR21455
- CE



30 & 60 Amp:

- Clip, Copper Alloy, Tin Plated

100 Amp:

- Clip, Copper Alloy, Tin Plated



200 Amp:

- Clip, One Piece Aluminum, Tin Plated

400 & 600 Amp:

- Clip, Copper Alloy, Tin Plated

Catalog #:

Std.	Reinforced	Poles	Amp	Base Materials	Wire Range	Fuse Size	Fuses
F30A1S	RF30A1S	1	30	Thermoplastic	#10-#22 AWG CU	9/16" DIA BY 2"	A2Y CRN NLN NON NRN OT OTN RLN RF
F30A2S	RF30A2S	2			#10-#14 AWG CU		
F30A3S	RF30A3S	3			#6-#14 AWG CU		
F30A1SP	RF30A1SP	1			#10-#22 AWG CU		
F30A2SP	RF30A2SP	2			#2-#14 AWG CU		
F30A3SP	RF30A3SP	3			#2-#12 AWG AL		
F60A1B	RF60A1B	1	60	Phenolic	#10-#22 AWG CU	13/16" DIA BY 3"	
F60A2B	RF60A2B	2			#2-#14 AWG CU		
F60A3B	RF60A3B	3			#2-#12 AWG AL		
F60A1SQ*	RF60A1SQ*	1			#10-#22 AWG CU		
F60A2SQ*	RF60A2SQ*	2			#2-#14 AWG CU		
F60A3SQ*	RF60A3SQ*	3			#2-#12 AWG AL		
RF100A1B	SAME	1	100	Phenolic	#2/0-#14 AWG CU	1" DIA BY 5 7/8"	
RF100A2B		2			#2/0-#12 AWG AL		
RF100A3B		3					
F200A1BE	SAME	1	200	Polyester	250 MCM- #6 AWG CU AL	1 1/2" DIA BY 7 1/8"	
F200A3BE		3					
RF400A1B	N/A	1	400	Phenolic	(2) 350 MCM- #6 AWG CU AL	2 13/32" DIA BY 8 5/8"	
RF400A3B		3					
F600A1B	N/A	1	600	Phenolic	(2) 500 MCM- #4 AWG CU AL	2 29/32" DIA BY 10 3/8"	
F600A3B		3					



*UL Recognized File No. E35113
Contact Factory for Stud Options

