



Class H & K Fuse Holder - 250 Volt

Specifications:

- Have Been Tested & Approved for 10,000 Amp Interrupting Capacity
- Patented Cool Clip® Design
- UL Listed File No. E35113
- CSA Cert. File No. LR21455
- CE



30 & 60 Amp:



- Clip, Copper Alloy, Tin Plated

100 Amp:

- Clip, Copper Alloy, Tin Plated

200 Amp:

- Clip, One Piece Aluminum, Tin Plated

400 & 600 Amp:

- Clip, Copper Alloy, Tin Plated

Catalog #:

Std.	Reinforced	Poles	Amp	Base Materials	Wire Range	Fuse Size	Fuses				
F30A1S	RF30A1S	1	30	Thermoplastic	#10-#22 AWG CU	9/16" DIA BY 2"	A2Y CRN NLN NON NRN OT OTN RLN RF				
F30A2S	RF30A2S	2									
F30A3S	RF30A3S	3									
F30A1SP	RF30A1SP	1									
F30A2SP	RF30A2SP	2									
F30A3SP	RF30A3SP	3									
F30A1B	RF30A1B	1									
F30A2B	RF30A2B	2									
F30A3B	RF30A3B	3									
F60A1SQ*	RF60A1SQ*	1	60	Thermoplastic	#10-#22 AWG CU	13/16" DIA BY 3"	A2Y CRN NLN NON NRN OT OTN RLN RF				
F60A2SQ*	RF60A2SQ*	2									
F60A3SQ*	RF60A3SQ*	3									
F60A1B	RF60A1B	1									
F60A2B	RF60A2B	2									
F60A3B	RF60A3B	3									
RF100A1B	SAME	1			100			Phenolic	#2/0-#14 AWG CU	1" DIA BY 5 7/8"	A2Y CRN NLN NON NRN OT OTN RLN RF
RF100A2B		2									
RF100A3B		3									
F200A1BE	SAME	1	200	Polyester	250 MCM-	1 1/2" DIA BY 7 1/8"	A2Y CRN NLN NON NRN OT OTN RLN RF				
F200A3BE		3									
RF400A1B		1									
RF400A3B	3	400	Phenolic	(2) 350 MCM- #6 AWG CU AL	2 13/32" DIA BY 8 5/8"	A2Y CRN NLN NON NRN OT OTN RLN RF					
F600A1B	1	600		(2) 500 MCM- #4 AWG CU AL	2 29/32" DIA BY 10 3/8"						
F600A3B	3										

*UL Recognized File No. E35113
Contact Factory for Stud Options

