

# Drive Fuse

## High Speed Fuses

### Class J - 600 Volt

**CROSS REF  
FOR  
30100-449-13**

**DFJ  
1 to 600A**



**Catalog Symbol:** DFJ  
High Speed Fuse

**Current-Limiting**

**Ampere Rating:** 1 to 600A

**Voltage Rating:** 600Vac (or less), 450Vdc (or less)

**Interrupting Rating:** 200,000A RMS Sym., 100,000A dc

**Agency Information:**


UL Listed, Std. 248-8, Class J, Guide JDDZ, File E4273

CSA Certified, C22.2 No. 248.8, Class 1422-02, File 53787


**Catalog Numbers (Amps)**

DFJ-1	DFJ-15	DFJ-70	DFJ-225
DFJ-2	DFJ-20	DFJ-80	DFJ-250
DFJ-3	DFJ-25	DFJ-90	DFJ-300
DFJ-4	DFJ-30	DFJ-100	DFJ-350
DFJ-5	DFJ-35	DFJ-110	<b>DFJ-400</b>
DFJ-6	DFJ-40	DFJ-125	DFJ-450
DFJ-8	DFJ-45	DFJ-150	DFJ-500
DFJ-10	DFJ-50	DFJ-175	DFJ-600
DFJ-12	DFJ-60	DFJ-200	

**Dimensional Data - 1-60A**



**1A to 30A**



**35A to 60A**


**Combine the performance of high speed semiconductor fuses and the convenience of Class J branch circuit fuses in one package.**

The new Cooper Bussmann® Drive Fuse will provide maximum protection for AC and DC drives and controllers and meet NEC® branch circuit protection requirements. The Drive Fuse has the lowest I<sup>2</sup>t of any branch circuit fuse to protect power semiconductor devices that utilize diodes, GTO's, SCR's and SSR's.

**General Information:**

- Easily coordinated with existing and new variable speed drives and electronic controllers.
- Standard Class J dimensions allowing the use of readily available fuse blocks, holders, and switches.
- Allows the lowest let-thru energy of any branch circuit overcurrent protective device.

**Dimensional Data - 70-600A**



**70A to 100A**

