

3 PHASE VOLTAGE TRANSFORMER

Model 2VT469

FREQUENCY:
60 Hz

STANDARD
SECONDARY VOLTAGE:
120 Volts

INSULATION LEVEL:
600 Volt, 10 kV BIL full wave.

ACCURACY CLASS:
± 1% at all burdens up to 5 VA at
1.0 and 0.95 P.F.

THERMAL RATING:
40 VA at 30°C, amb.,
27 VA at 55°C, amb.

REGULATORY AGENCY APPROVALS





E93779 LR89403



Manufactured to meet the requirements of ANSI/IEEE C57.13.
Classified by ILL in accordance with IEC 44-2

See page 14 & 15 for 3 phase 4 wire connected version.

- The core and coil assembly is encased in a thermoplastic shell and filled with resin.
- These transformers are designed for operation line-to-line. They may also be operated line-to-ground or line-to-neutral at reduced voltage, (58% of rated volts).
- Terminals are No. 6-32 screws with one lockwasher and one flatwasher.
- It is desirable to use a 0.40 amp fuse in the secondary to protect the transformer.
- With two exceptions these transformers are ANSI C57.13 group 1. Those marked * are group 2.
- Models designed specifically for 50Hz operation are available with reduced performance consult factory for details.
- Model 469 is an assembly of two transformers in one case with all terminals accessible, for open delta connection.
- Each transformer has a clear plastic terminal cover.
- Approximate weight: 4.5 lbs.



CATALOG NUMBER	VOLTAGE RATING	TURNS RATIO	REC. PRIMARY FUSE RATING
469-069	69.3:120	0.58:1	1.5
469-120	120:120	1:1	1.0
469-208	208:120	1.73:1	0.5
469-240	240:120	2:1	0.5
469-277	277:120	2.31:1	0.5
469-288	288:120	2.4:1	0.4
469-300	300:120	2.5:1	0.4
469-346	346:120	2.88:1	0.4
*469-480	*480:120	4:1	0.25
*469-600	*600:120	5:1	0.25

469 CONNECTION DIAGRAM

