





- NOTES:
- 1) ALL DIMENSIONS ARE +/- 0.06 UNLESS OTHERWISE NOTED.
  - 2) TRANSFORMER IS CSA CERTIFIED (LR3902-88M) AND UL LISTED (E50394 & LISTING #252L) AS TYPE 3AH.
  - 3) CE MARKED PER REQUIREMENTS OF IEC 989:1991 AND RELEVANT SECTIONS OF EC LOW VOLTAGE DIRECTIVE 73/23/EEC.
  - 4) TRANSFORMER IS TERMINATED WITH TERMINAL BLOCK SUITABLE FOR #14 AWG MAX LEADS.
  - 5) NAMEPLATE TO BE OBTAINED FROM ALLEN-BRADLEY CO, OR SUPPLIER. STAMP NAMEPLATE WITH A-B PART NUMBER, PRIMARY AND SECONDARY VOLTAGES, FREQUENCIES, AND KVA. UL RECOGNIZED "TYPE" DESIGNATION AND CSA "FILE NUMBER" MUST BE STAMPED BY EACH SUPPLIER ON THE NAMEPLATE.
  - 6) VPI GLOSS BLACK FINISH OVER ENTIRE TRANSFORMER. WELDED CORE CONSTRUCTION ACCEPTABLE. 55°C TEMPERATURE USE CLASS B (130°C) INSULATION.
  - 7) SECONDARY JUMPERS ARE INCLUDED BETWEEN X1-X3, X2-X4.

$\triangle$   
(2) - .188 DIA.



PRIMARY VOLTAGE	SUPPLY LINES CONNECT TO	SECONDARY VOLTAGE	LOAD LINES CONNECT TO	INSTALL JUMPERS BETWEEN
380	H1-H2	110-115	X1-X4	X1-X3, X2-X4
400	H1-H3	110-115	X1-X4	X1-X3, X2-X4
415	H1-H4	110-115	X1-X4	X1-X3, X2-X4
380	H1-H2	220-230	X1-X4	X2-X3
400	H1-H3	220-230	X1-X4	X2-X3
415	H1-H3	240	X1-X4	X2-X3



PARTS MUST CONFORM TO APPLICABLE ALLEN-BRADLEY CO. WORKMANSHIP STANDARD 40126-700



PART NUMBER	CHANGE LETTER
-01	B

REFERENCES	NONE
REVISION	DIMENSIONS APPLY BEFORE SURFACE TREATMENT
RELEASE	(DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED
1 21253-97	2 PLACE DECIMAL (.XX) ± .02
2 21110-98	3 PLACE DECIMAL (.XXX) ± .005
3 21267-98	ANGLES ± 1°

COMPACT 50VA TRANSFORMER		CV 40121.463.R3.REM	
50/60 HZ		 ALLEN-BRADLEY A ROCKWELL INTERNATIONAL COMPANY <small>THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.</small>	
DR. K.L. JENNINGS	DATE 8-29-97	SHEET 1 OF 1	 40121-463
CHKD. N/A	DATE N/A		
APPD. G. BRUSKI	DATE 8-29-97		