


HBL1221PL



Red polycarbonate toggle switch

Hubbell Wiring Device-Kellems Product Specifications

Type	General Purpose AC
Actuator Type	Toggle
Toggle Type	Pilot
Switch Type for General Purpose AC	Single Pole/Single Throw
Grade	Industrial
Amperage	20A
Voltage	120/277V AC
Termination Type for General Purpose AC	Back and Side Wired
Color	 Red
Switch Positions	2
Contact Type	Maintained
Approvals	UL Listed, CSA Certified, Listed to FED. Spec. W-S-896E
Base Material	Thermoset, Color Coded by Amperage
Top Material	Thermoset, Gray
Toggle Material	Polycarbonate
Terminals Material	Brass
Terminal Screw Material	Brass

Mounting Strap Material	Nickel Plated Steel
Contacts Material	Silver Cadmium Oxide
Moveable Contact Arm Material	Brass
Rocker Material	Neoprene
Ground Terminal Material	Nickel-Plated Steel
Ground Screw Material	Brass
Automatic Grounding Clip Material	Stainless Steel
Dielectric Voltage Withstand	1500V minimum
Max. Working Voltage	277V AC
Overload	Minimum 4.8 times rated current for 100 cycles
Temperature Rise	30°C maximum at rated current
Endurance	50,000 cycles min., tungsten filament lamp load (Fed. Spec) #WS896E
Terminal Accommodation	#14 AWG min. - #10 AWG max.
Flammability	UL 94 V2.
Operating Temperature	Max. continuous: 75° C; Min. continuous: -40° C w/o impact

Horsepower Conversion Chart

	120V	240V
15A	1 HP	2HP
20A	1½HP	2HP
30A	2HP	2HP

