



Hammond Power Solutions Inc.

GUELPH, ONT. BARABOO, WI COMPTON, CA MONTERREY, MX




LR 3902
 DRY TYPE TRANSFORMER
 77US
 E112313
LISTED

HPS SENTINEL
 ENERGY EFFICIENT GENERAL PURPOSE DISTRIBUTION (ISOLATION) TRANSFORMER

HV/HT	380V				Cust. Ref.	
BIL	-				Réf. du client	
TERM. BORNES	H1 H4				Serial No.	
					No. de série	
					Part No.	200755
					No. de pièce	
					Phase	1
					TYPE	F
					Cooling Refroidissement	ANN
					kVA	15
					Temp. Rise Echouffement	150 °C
					Temp. Class Classe de Temp.	220 °C
					Frequency Fréquence	60 Hz
					Impédance % @ 170 °C	5.7
LV/BT	115V				Encl. Type Type de boîtier	NEMA-3R
BIL	-				Wt LBS Poids en lbs.	210
TERM. BORNES	X2 X1				Winding Enroulement	CU

VOLTS	CURRENT COURANT	% RATED VOLTAGE % TENSION NOMINALE	CONNECTION EACH PHASE CONNEXION PAR PHASE
380	39.5	100	H1-H4
361	41.6	95	H1-H3
342	43.9	90	H2-H3



Energy Regulations
 Reglements de Energetique

CEE ACT
 SOR/94/651

ALSO VERIFIED IN ACCORDANCE WITH ENERGY STANDARD C8022-06 BY UNDERWRITERS LABORATORIES INC. © 3VJ6

SPACINGS BETWEEN ANY VENTILATED ENCLOSURE PANEL AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 3 INCHES

D0000821b




TITLE: 1PH DISTRIBUTION TRANSFORMER
 NAMEPLATE INFORMATION

DES:	RBHATIA		
DATE:	11/08/08		
SCALE:	NTS		
NO.	DATE	BY	REVISION

SHEET 1 OF 2
 EDB 200755

0.1 rbhata 2011/08/24 14:44



All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #14-2 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR 250MCM-6 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT COIL FACE
- LV1 TERMINATED AT BOTTOM FRONT



TITLE: 1PH DISTRIBUTION TRANSFORMER

				DES: RBHATIA
				DATE: 11/08/08
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 2 OF 2

EDB 200755

0.1 rbhatia 2011/08/24 14:44