

GENERAL NOTES:

- 1) OVERALL HEIGHT TO BE 3-5/16 MAXIMUM INCLUDING NAMEPLATE RIVET, IF USED.
- 2) 1/2" MINIMUM SPACING BETWEEN ADJACENT TERMINALS AND BETWEEN TERMINALS AND GROUND MEASURED ON COIL SURFACE.
- 3) IDENTIFY ALL TERMINALS ON SIDE OF COIL.
- 4) NAMEPLATE TO BE OBTAINED FROM ALLEN-BRADLEY CO. OR SUPPLIER. STAMP NAMEPLATE WITH A-B PART NUMBER, PRIMARY AND SECONDARY VOLTAGES, FREQUENCY, AND KVA. UL RECOGNIZED "TYPE" DESIGNATION AND CSA "FILE NUMBER" MUST BE STAMPED BY EACH SUPPLIER ON THE NAMEPLATE. MOUNT NAMEPLATE ON TRANSFORMER TO BE READ FROM THE SECONDARY SIDE, AND CENTER NAMEPLATE ON CORE TO PROVIDE SPACE FOR FUSE LABEL.
- 5) FLAT BLACK FINISH OVER ENTIRE TRANSFORMER.

X-183221	N	THIS DWG.	.130	550	16	60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183220	N	THIS DWG.	.130	380	220	50	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183219	N	THIS DWG.	.130	110	7	60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183218	P	THIS DWG.	.130	400	110	50/60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	46010-041-11	1497-N71
X-183217	N	THIS DWG.	.130	110	32	60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183216	N	THIS DWG.	.130	110	24	60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183215	N	THIS DWG.	.130	550	110	40	5	3-3/4	2-1/2	4-3/8	4-3/8	+3/16 -1/32	H-18969	NONE
X-183214	N	THIS DWG.	.130	160	110	50	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183213	N	THIS DWG.	.130	208	208	60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183212	N	THIS DWG.	.130	208	120	60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	45010-334-13	1497-N15
X-183211	N	THIS DWG.	.130	220	24	50	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183210	N	THIS DWG.	.130	550	220	60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183209	N	THIS DWG.	.130	440	24	60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183208	N	THIS DWG.	.060	460	230	25	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183207	N	THIS DWG.	.130	550	24	50/60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183206	N	THIS DWG.	.130	440	220	50/60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183205	P	THIS DWG.	.130	380	110	50	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	46010-041-12	1497-N72
X-183204	N	THIS DWG.	.130	380	24	50	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183203	N	THIS DWG.	.060	575	115	25	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	H-18969	NONE
X-183202	P	THIS DWG.	.130	600 550	120 110	60 50/60	4-1/2	3-1/4	2	3-7/8	3-7/8	+3/16 -1/32	45010-334-15	1497-N17
PART NO.	CHG. LTR.	MATERIAL	K.V.A.	PRIM. VOLTAGES	SEC. VOLTAGES	HERTZ	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	DIM. "E"	DIM. "E" TOL.	NAME PLATE	CAT. NO. REF.

REFERENCE

REVISION AUTHORIZATION	
12	2075-96
13	2075C-96

DIMENSIONS APPLY BEFORE SURFACE TREATMENT


(DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED

xx: ±

xxx: ±

ANGLES: ±

SINGLE VOLTAGE CONTROL TRANSFORMER



DR. Lynn Mickelson	DATE 5-4-99
CHKD. Mark Jutz	DATE 5-4-99
APPD. Joe Koziczowski	DATE 5-4-99

MAC DOCUMENT

THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.

LOCATION: MILWAUKEE, WISCONSIN U.S.A.

DWG SIZE	SHEET 1 OF 1
B	X-183202-21