


GENERAL NOTES:

- 1) 1/2" MINIMUM SPACING BETWEEN ADJACENT TERMINALS AND BETWEEN TERMINALS AND GROUND MEASURED ON COIL SURFACE.
- 2) IDENTIFY ALL TERMINALS ON SIDE OF COIL.
- 3) NAMEPLATE TO BE OBTAINED FROM ALLEN-BRADLEY CO. OR SUPPLIER. STAMP NAMEPLATE WITH A-B PART NUMBER, PRIMARY AND SECONDARY VOLTAGES, FREQUENCY, AND KVA. UL RECOGNIZED "TYPE" DESIGNATION AND CSA "FILE NUMBER" MUST BE STAMPED BY EACH SUPPLIER ON THE NAMEPLATE. MOUNT NAMEPLATE ON TRANSFORMER TO BE READ FROM THE SECONDARY SIDE, AND CENTER NAMEPLATE ON CORE TO PROVIDE SPACE FOR FUSE LABEL.
- 4) FLAT BLACK FINISH OVER ENTIRE TRANSFORMER.

REFERENCE		DUAL VOLTAGE CONTROL TRANSFORMER		MAC DOCUMENT	
REVISION AUTHORIZATION		DIMENSIONS APPLY BEFORE SURFACE TREATMENT		THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.	
4	2075-96	(DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED		LOCATION: MILWAUKEE, WISCONSIN U.S.A.	
		.XX: ±		DWG SIZE	
		.XXX: ±		SHEET 1 OF 2	
		ANGLES: ±		B X-211292-311	
DR. L.A. MICKELSON		DATE 3-31-97		APPD. <i>Joe L. Kozlowski</i>	
CHKD. <i>H. Mickelson</i>		DATE 3-31-97		DATE 3-31-97	



PART NO.	CHG. LTR.	MAT	K.V.A.	PRIMARY VOLTAGES	SECOND. VOLTAGES	HERTZ	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	DIM. "E"	NAME PLATE	CAT. NO. REF.	REMARKS
X-211311	H	THIS DWG.	.500	240/480/600 220/440/550	120	60	6-3/4	4-5/8	2-7/8	5-1/2	5-13/16	H-18969	NONE	
X-211310	K	THIS DWG.	.500	240/480	120	60	6	4-1/8	2-3/8	5	5-5/16	H-18969	NONE	
X-211309	F	THIS DWG.	.500	550	110/220	60	6	4-1/8	2-3/8	5	5-5/16	H-18969	NONE	
X-211306	F	THIS DWG.	.500	220/440	115/110/105	50/60	6-3/4	4-5/8	2-7/8	5-1/2	5-13/16	H-18969	NONE	FULL RATING ALL TAPS
X-211307	F	THIS DWG.	.500	208/220/440	110	50/60	6-3/4	4-5/8	2-7/8	5-1/2	5-13/16	H-18969	NONE	220 EXTENDED FOR 208
X-211306	F	THIS DWG.	.500	380	115/110/105	50	6-3/4	4-5/8	2-7/8	5-1/2	5-13/16	H-18969	NONE	
X-211305	F	THIS DWG.	.500	220/440	110/24	60	6	4-1/8	2-3/8	5	5-5/16	H-18969	NONE	(110V-500VA) (24V-100VA)
X-211304	F	THIS DWG.	.500	380/220	110	50	6-3/4	4-5/8	2-7/8	5-1/2	5-13/16	H-18969	NONE	
X-211303	F	THIS DWG.	.500	200	110/93	50/60	6-1/4	4-3/8	2-5/8	5-1/4	5-9/16	H-18969	NONE	
X-211302	F	THIS DWG.	.500	240/480	110	60	6	4-1/8	2-3/8	5	5-5/16	H-18969	NONE	
X-211301	F	THIS DWG.	.500	220/440	110/220	60	6	4-1/8	2-3/8	5	5-5/16	H-18969	NONE	
X-211300	F	THIS DWG.	.500	220/440	24	50/60	6-1/4	4-3/8	2-5/8	5-1/4	5-9/16	H-18969	NONE	
X-211299	F	THIS DWG.	.500	380/220	24	50	6-3/4	4-5/8	2-7/8	5-1/2	5-13/16	H-18969	NONE	
X-211298	F	THIS DWG.	.500	220/440	110	50/60	6-1/4	4-3/8	2-5/8	5-1/4	5-9/16	H-18969	NONE	CLASS B INSULATED
X-211297	F	THIS DWG.	.500	240/480	120/240	60	6	4-1/8	2-3/8	5	5-5/16	H-18969	NONE	
X-211296	F	THIS DWG.	.500	220/440	80/65/50	60	6-1/4	4-3/8	2-5/8	5-1/4	5-9/16	H-18969	NONE	FULL VA RATING AT 80V ONLY
X-211295	K	THIS DWG.	.500	220/440	110/93	50/60	6-1/4	4-3/8	2-5/8	5-1/4	5-9/16	H-18969	NONE	
X-211294	F	THIS DWG.	.275	220/440	110	25	6-1/4	4-3/8	2-5/8	5-1/4	5-9/16	H-18969	NONE	500 VA FRAME
X-211293	J	THIS DWG.	.500	240/480 220/440	120 110	60 50/60	6-1/4	4-3/8	2-5/8	5-1/4	5-9/16	45010-334-17	1497-N19	
X-211292	K	THIS DWG.	.500	220/440	110	60	6	4-1/8	2-3/8	5	5-5/16	H-18969	NONE	

REVISION AUTHORIZATION 4 2075-96		DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED XX: ± XXX: ± ANGLES: ±		DUAL VOLTAGE CONTROL TRANSFORMER					MAC DOCUMENT THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.			
								LOCATION: MILWAUKEE, WISCONSIN U.S.A.				
				DR. L.A. MICKELSON		DATE 3-31-97		DWG SIZE SHEET 2 OF 2		X-211292-311		
				CHKD. _____		DATE _____		B				
				APPD. _____		DATE _____						