



GENERAL NOTES:

- 1) 1/2" MINIMUM SPACING BETWEEN ADJACENT TERMINALS AND BETWEEN TERMINALS AND GROUND MEASURED ON COIL SURFACE.
- 2) IDENTIFY ALL TERMINALS ON SIDE OF COIL.
- 3) NAMEPLATE TO BE OBTAINED FROM ALLEN-BRADLEY CO. OR SUPPLIER. STAMP NAMEPLATE WITH A-B PART NUMBER, PRIMARY AND SECONDARY VOLTAGES, FREQUENCY, AND KVA. UL RECOGNIZED "TYPE" DESIGNATION AND CSA "FILE NUMBER" MUST BE STAMPED BY EACH SUPPLIER ON THE NAMEPLATE. MOUNT NAMEPLATE ON TRANSFORMER TO BE READ FROM THE SECONDARY SIDE, AND CENTER NAMEPLATE ON CORE TO PROVIDE SPACE FOR FUSE LABEL.
- 4) FLAT BLACK FINISH OVER ENTIRE TRANSFORMER.
- 5) LENGTH OF BOLT AND NUT PROTRUDING FROM THE BRACKET 5/16" MAX.

PARTIALLY DISCONTINUED		
DISCONTINUED DATE: 3-82		
P.O.N.	ECN	NO.
75-37A	7723-76	1
PARTS: X-211483		
REINSTATED 3-16-83		

REFERENCE	X-313717-31	SINGLE VOLTAGE CONTROL TRANSFORMER	MAC DOCUMENT
REVISION AUTHORIZATION			THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC. LOCATION: MILWAUKEE, WISCONSIN U.S.A.
DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED .xx: ± .xxx: ± ANGLES: ±			
10	2075-96	DR. Lynn Mickelson	DATE 1-21-00
11	2075C-96	CHKD. Mark Jutz	DATE 1-21-00
		APPD. Joe Koziczowski	DATE 1-21-00
		DWG SIZE	SHEET 1 OF 2
		B	X-211467-486

A
B
C
D
E
F
G
H

PARTIALLY DISCONTINUED		
DISCONTINUED DATE: 3-82		
P.O.N.	ECN	NO.
75-37A	7723-76	1
PARTS: X-211483		

REINSTATED 3-16-83

X-211486	M	PER THIS DWG.	.350	240	120	60	H-18969	NONE	
X-211485	M	PER THIS DWG.	.350	600	110	60	H-18969	NONE	
X-211484	M	PER THIS DWG.	.350	208	110	60	H-18969	NONE	
X-211483	E	PER THIS DWG.	.350	400	110	50	H-18969	NONE	OBSOLETE
X-211482	M	PER THIS DWG.	.350	525	110	50/60	H-18969	NONE	
X-211481	M	PER THIS DWG.	.350	110	24	60	H-18969	NONE	
X-211480	M	PER THIS DWG.	.300	705	93	50	H-18969	NONE	
X-211479	M	PER THIS DWG.	.350	550	120	50/60	H-18969	NONE	
X-211478	M	PER THIS DWG.	.350	208	120	60	45010-334-10	1497-N10	
X-211477	M	PER THIS DWG.	.350	200	110	50	H-18969	NONE	
X-211476	M	PER THIS DWG.	.350	416	120	60	H-18969	NONE	
X-211475	M	PER THIS DWG.	.350	500	110	50	H-18969	NONE	
X-211474	M	PER THIS DWG.	.350	380	110	50	H-18969	NONE	
X-211473	N	PER THIS DWG.	.350	208	24	60	46010-041-01	1497-N60	
X-211472	M	PER THIS DWG.	.350	120	24	50/60	H-18969	NONE	
X-211471	M	PER THIS DWG.	.350	550	220	50/60	H-18969	NONE	
X-211470	M	PER THIS DWG.	.350	440	220	50/60	H-18969	NONE	
X-211469	M	PER THIS DWG.	.350	440	24	50/60	H-18969	NONE	
X-211468	M	PER THIS DWG.	.175	550	110	25	H-18969	NONE	
X-211467	N	PER THIS DWG.	.350	600 550	120 110	60 50/60	45010-334-12	1497-N12	
PART NO.	CHG. LTR.	MATERIAL	K.V.A.	PRIMARY VOLTAGES	SECONDARY VOLTAGES	HERTZ	NAME PLATE	CAT. NO. REF.	REMARKS



REFERENCE	X-313717-31	SINGLE VOLTAGE CONTROL TRANSFORMER	MAC DOCUMENT				
REVISION AUTHORIZATION <table border="1" style="width: 100%;"> <tr><td>10</td><td>2075-96</td></tr> <tr><td>11</td><td>2075C-96</td></tr> </table>		10	2075-96	11	2075C-96	 Allen-Bradley 	THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC. LOCATION: MILWAUKEE, WISCONSIN U.S.A.
10	2075-96						
11	2075C-96						
DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED .XX: ± .XXX: ± ANGLES: ±		DR. Lynn Mickelson DATE 1-21-00 CHKD. _____ DATE _____ APPD. _____ DATE _____					
		B	DWG. SIZE: SHEET 2 OF 2 X-211467-486				