



GENERAL NOTES:

- 1) OVERALL HEIGHT TO BE 3-5/16 MAXIMUM INCLUDING NAMEPLATE.
- 2) 1/2" MINIMUM SPACING BETWEEN ADJACENT TERMINALS AND BETWEEN TERMINALS AND GROUND MEASURED ON COIL SURFACE.
- 3) IDENTIFY ALL TERMINALS ON SIDE OF COIL.
- 4) NAMEPLATE TO BE OBTAINED FROM ALLEN-BRADLEY CO. OR SUPPLIER. STAMP NAMEPLATE WITH A-B PART NUMBER, PRIMARY AND SECONDARY VOLTAGES, FREQUENCY, AND KVA. UL RECOGNIZED "TYPE" DESIGNATION AND CSA "FILE NUMBER" MUST BE STAMPED BY EACH SUPPLIER ON THE NAMEPLATE. MOUNT NAMEPLATE ON TRANSFORMER TO BE READ FROM THE SECONDARY SIDE, AND CENTER NAMEPLATE ON CORE TO PROVIDE SPACE FOR FUSE LABEL.
- 5) FLAT BLACK FINISH OVER ENTIRE TRANSFORMER.
- 6) MOUNT LABEL ON TRANSFORMER TO BE READ FROM THE SECONDARY SIDE AS SHOWN.

REFERENCE		DUAL VOLTAGE CONTROL TRANSFORMER		MAC DOCUMENT	
REVISION AUTHORIZATION				THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.	
11	2075-96	 		LOCATION: MILWAUKEE, WISCONSIN U.S.A.	
DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED				DR. L.A. MICKELSON DATE 3-27-97 CHKD. <i>H. Mickelson</i> DATE 3-28-97 APPD. <i>Joe Kozigowski</i> DATE 3-31-97	
xx. ±		DWG. SIZE: B		SHEET 1 OF 2	
.xxx. ±				X-183222-41	
ANGLES: ±					

A
B
C
D
E
F
G

04-10-97

X-183241	K	THIS DWG.	.130	240/480	110	50/60	H-18969	NONE	H-22014	
X-183240	K	THIS DWG.	.130	110/220	24	60	H-18969	NONE	H-22014	
X-183239	K	THIS DWG.	.130	380	110/93	50/60	H-18969	NONE	H-22014	
X-183238	K	THIS DWG.	.130	420	110/93	50/60	H-18969	NONE	H-22014	
X-183237	K	THIS DWG.	.130	93	32/30/28	50	H-18969	NONE	42006-055-01	FULL CAP. EACH TAP
X-183236	K	THIS DWG.	.130	200/400/500	110/93	50/60	H-18969	NONE	42006-055-01	
X-183235	L	THIS DWG.	.130	220/440/550	110/93	50/60	H-18969	NONE	42006-055-01	
X-183234	K	THIS DWG.	.130	110	32/30/28	60	H-18969	NONE	42006-055-01	FULL CAP. EACH TAP
X-183233	K	THIS DWG.	.130	110	6-110	60	H-18969	NONE	H-22014	6V WDG 50VA 110V WDG 75VA
X-183232	K	THIS DWG.	.130	220/440	24	60	H-18969	NONE	H-22014	
X-183231	K	THIS DWG.	.130	220/440	32	60	H-18969	NONE	H-22014	
X-183230	K	THIS DWG.	.130	415	110/32	50	H-18969	NONE	H-22014	32V TAP 110VA 110V TAP 30VA
X-183229	K	THIS DWG.	.130	220/440	12	60	H-18969	NONE	H-22014	
X-183228	K	THIS DWG.	.130	220/440	110/32	50/60	H-18969	NONE	H-22014	32V TAP 60VA 110V TAP 70VA
X-183227	K	THIS DWG.	.130	230/460	115/95	50/60	H-18969	NONE	H-22014	
X-183226	K	THIS DWG.	.060	110/220	16	25	H-18969	NONE	H-22014	
X-183225	K	THIS DWG.	.130	380/220	110	50	H-18969	NONE	SPECIAL	
X-183224	K	THIS DWG.	.130	230/460	115/230	50/60	H-18969	NONE	H-22014	DUAL WOUND PRI. & SEC.
X-183223	K	THIS DWG.	.060	220/440	110	25	H-18969	NONE	H-22014	
X-183222	K	THIS DWG.	.130	220/440 240/480	110 120	50/60 60	45010-334-14	1497-N16	H-22014	
PART NO.	CHG. L.Y.R.	MAT	K.V.A.	PRIMARY VOLTAGES	SECOND. VOLTAGES	HERTZ	NAME PLATE	CAT. NO. REF.	WIRING DIA. SEE NOTE 6	REMARKS



REFERENCE REVISION AUTHORIZATION 11 2075-96 DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED .XX: ± .XXX: ± ANGLES: ±		DUAL VOLTAGE CONTROL TRANSFORMER 				MAC DOCUMENT THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC. LOCATION: MILWAUKEE, WISCONSIN U.S.A.	
DR. L.A. MICKELSON CHKD. APPD.		DATE 3-27-97 DATE DATE		DWG. SIZE SHEET 2 OF 2 B X-183222-41			