



A-B NAMEPLATE (SEE TABLE)
 STAMP NAMEPLATE WITH CATALOG OR PART
 NUMBER, PRIM. & SEC. VOLTAGES AND HERTZ,
 AND KVA AS SHOWN.

ALLEN-BRADLEY NAMEPLATE FURNISHED TO
 SUPPLIER ON REQUEST. NAMEPLATE TO BE
 STAMPED BY SUPPLIER AS DIRECTED AND
 MOUNTED ON THE TRANS. TO READ FROM THE
 SECONDARY SIDE.

1/2" MINIMUM SPACING BETWEEN ADJACENT
 TERM. & BETWEEN TERM. AND GROUND
 MEASURED ON COIL SURFACE.

FLAT BLACK FINISH OVER ENTIRE
 TRANSFORMER.

IDENTIFY ALL TERMINALS ON SIDE OF COIL.

UL RECOGNIZED "TYPE" DESIGNATION AND CSA
 "FILE NUMBER" MUST BE STAMPED BY EACH
 SUPPLIER ON ALLEN-BRADLEY NAMEPLATE.

PART NO.	CHG. LTR.	K.V.A.	VOLTAGES		HERTZ	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	NAME PLATE	CAT. NO. REF.	REMARKS
			PRIM.	SEC.								
X-231423	K	.750	240/480 220/440	120 110	60 50/60	7-1/8		6-1/8	4-3/8	45010-334-23	1497-N34	
X-231424	H	.350	220/440	110	25	6-7/8		5-7/8	4-1/8	H-18969	NONE	
X-231425	J	.750	220/440	110/93	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231426	H	.750	290	110/93	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231427	H	.750	220/440	110/220	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231428	H	.750	380	110/93	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231429	H	.750	500	110/93	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231430	H	.750	220/440	110/24	60	6-3/4		6-3/4	4	H-18969	NONE	24V TAP 30VA
X-231431	H	.750	220/440/550	110	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231432	H	.750	110/220	110/93	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231433	H	.750	400	110/93	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231434	H	.750	440	135/110/65/25	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231435	H	.750	440	120/100/80/60	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	ALL TAPS RATED 500VA
X-231436	H	.750	200/400	110	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231437	H	.750	200	110/93	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231438	H	.750	200/400	110/93	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231439	H	.750	380	220/110	50	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231440	H	.750	240/480	110	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231441	H	.750	415	110/93	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231442	H	.750	380/220	24	50	7-7/8		6-7/8	5-1/8	H-18969	NONE	NOTE 1: 10-32 UNF-2B
X-231443	H	.750	460	125/115	50/60	7-1/8		6-1/8	4-3/8	H-18969	NONE	
X-231444	H	.750	220/440	110/12	60	6-3/4		5-3/4	4	H-18969	NONE	12V TAP 50VA
X-231445	H	.750	220/440	110	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231446	J	.750	240/480	120	60	6-3/4		5-3/4	4	H-18969	NONE	
X-231447	H	.750	380/220	110/95	50/60	7-7/8		6-7/8	5-1/8	H-18969	NONE	

REFERENCE		CONT. XFMR. 0.750 KVA FRAME SIZE EQUIVALENT TO HEVI-DUTY S20 CONTROL TRANSFORMER DESIGN		MAC DOCUMENT	
REVISION AUTHORIZATION 4 2075-96				THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.	
DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED .XX: ± .XXX: ± ANGLES: ±				LOCATION: MILWAUKEE, WISCONSIN U.S.A.	
DR. L.A. MICKELSON CHKD. <i>L.A. Mickelson</i> APPD. <i>Joe Logezkowski</i>		DATE 3-31-97 DATE 3-31-97 DATE 3-31-97		DWG SIZE B SHEET 1 OF 1 X-231423-447	