


Model C10.0 Medium Voltage Current Transformer
Maximum System Voltage 15.5kv, BIL 110 kV full wave

**CROSS REF
 FOR
 X-316014**



- **UL and cUL Recognized**
- **As per ANSI/IEEE C57.13 OR IEC 60044 OR relevant standard**

INSULATION LEVEL

15.5 Kv, BIL 110 Kv full wave

FREQUENCY

50-400 Hz

CONTINUOUS THERMAL CURRENT RATING FACTOR

1.5 @ 30 deg. C ambient

1.33 @ 55 deg. C ambient

OUTER ENCAPSULATION

Polyurethane/Epoxy Resin Encapsulated

PRIMARY TERMINALS

Plated copper bars

SECONDARY TERMINALS

10-32 Brass screw with one flat washer and lock washer

APPROX. WEIGHT

75 lbs.

PLATED STEEL MOUNTING BASE


Mounting holes/dimensions as per customer requirement at no additional cost

CUSTOM OPTIONS (CONTACT US)

- Different Ratios, Accuracies
- Non-standard thermal rating
- Different encapsulation
- Different secondary termination
- Special mounting needs etc.

Catalog Number	Current Ratio	Accuracy (60 Hz)					
		Relay Class	ANSI metering Class				
			B0.1	B0.2	B0.5	B0.9	B1.8
C10.0-400	40:5	T20	1.2	-	-	-	-
C10.0-500	50:5	T30	0.6	2.4	-	-	-
C10.0-750	75:5	T45	0.6	1.2	2.4	-	-
C10.0-101	100:5	T60	0.6	0.6	1.2	2.4	-
C10.0-151	150:5	T100	0.3	0.3	0.6	1.2	2.4
C10.0-201	200:5	T120	0.3	0.3	0.3	0.6	1.2
C10.0-301	300:5	T100	0.3	0.3	0.6	1.2	2.4
C10.0-401	400:5	T80	0.3	0.3	0.3	0.3	0.6
C10.0-601	600:5	T100	0.3	0.3	0.3	0.3	0.3
C10.0-801	800:5	T120	0.3	0.3	0.3	0.3	0.3
C10.0-102	1000:5	T150	0.3	0.3	0.3	0.3	0.3
C10.0-122	1200:5	T200	0.3	0.3	0.3	0.3	0.3

- DIMENSIONS:**



ALL DIMENSIONS ARE IN INCHES [MM]