



GENERAL NOTES:

- 1) 1/2" MINIMUM SPACING BETWEEN ADJACENT TERMINALS AND BETWEEN TERMINALS AND GROUND MEASURED ON COIL SURFACE.
- 2) IDENTIFY ALL TERMINALS ON SIDE OF COIL.
- 3) NAMEPLATE TO BE OBTAINED FROM ALLEN-BRADLEY CO. OR SUPPLIER. STAMP NAMEPLATE WITH A-B PART NUMBER, PRIMARY AND SECONDARY VOLTAGES, FREQUENCY, AND KVA. UL RECOGNIZED "TYPE" DESIGNATION AND CSA "FILE NUMBER" MUST BE STAMPED BY EACH SUPPLIER ON THE NAMEPLATE. MOUNT NAMEPLATE ON TRANSFORMER TO BE READ FROM THE SECONDARY SIDE.
- 4) FLAT BLACK FINISH OVER ENTIRE TRANSFORMER.
- 5) SEE K-20-191 FOR DESIGN AND TEST SPECIFICATIONS.
- 6) MOUNTING HOLES MUST ACCEPT .195 DIAMETER PINS ON 2.375 X 2.812 CENTERS.
- 7) MOUNT LABEL ON XFMR TO READ FROM THE SECONDARY SIDE AS SHOWN.

REFERENCE		DUAL VOLTAGE CONTROL TRANSFORMER		MAC DOCUMENT	
REVISION AUTHORIZATION				THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.	
17	2075-96	DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED .XX: ± .XXX: ± ANGLES: ±		LOCATION: MILWAUKEE, WISCONSIN U.S.A.	
18	2075C-96				
		DR. Lynn Mickelson	DATE 5-4-99	DWG. SIZE	SHEET 1 OF 2
		CHKD. Mark Jutz	DATE 5-4-99	B	X-343858-907
		APPD. Joe Kozickowski	DATE 5-4-99		

PART NO.	CHG. LTR.	MATERIAL	K.V.A.	PRIMARY VOLTAGES	SECONDARY VOLTAGES	HERTZ	NAME PLATE	CAT. NO. REF.
X-343882	J	AS PER THIS DWG.	.075	190/380	115	50	H-18969	NONE
X-343881	J	AS PER THIS DWG.	.075	240/480	12	60	H-18969	NONE
X-343880	J	AS PER THIS DWG.	.075	220/380	120	50	H-18969	NONE
X-343879	J	AS PER THIS DWG.	.075	220/380	127	50	H-18969	NONE
X-343878	J	AS PER THIS DWG.	.075	200/400	110	60	H-18969	NONE
X-343877	J	AS PER THIS DWG.	.075	200/400	200	50	H-18969	NONE
X-343876	J	AS PER THIS DWG.	.075	190/380	95	50	H-18969	NONE
X-343875	J	AS PER THIS DWG.	.075	240/480	120	50	H-18969	NONE
X-343874	K	AS PER THIS DWG.	.075	110/220	6	60	H-18969	NONE
X-343873	K	AS PER THIS DWG.	.075	120/240	6	60	H-18969	NONE
X-343872	K	AS PER THIS DWG.	.075	120/240	12	60	H-18969	NONE
X-343871	K	AS PER THIS DWG.	.075	110/220	24	60	H-18969	NONE
X-343870	K	AS PER THIS DWG.	.075	220/440	24	60	H-18969	NONE
X-343869	K	AS PER THIS DWG.	.075	120/240	24	60	H-18969	NONE
X-343868	L	AS PER THIS DWG.	.075	240/480	24	60	45010-334-39	1497-N49
X-343867	K	AS PER THIS DWG.	.075	220/440	32	60	H-18969	NONE
X-343866	K	AS PER THIS DWG.	.075	240/480	32	60	H-18969	NONE
X-343865	K	AS PER THIS DWG.	.075	120/240	48	60	H-18969	NONE
X-343864	K	AS PER THIS DWG.	.075	110	32/30/28	60	H-18969	NONE
X-343863	K	AS PER THIS DWG.	.075	380/220	110	50	H-18969	NONE
X-343862	K	AS PER THIS DWG.	.075	415/240	110	50/60	H-18969	NONE
X-343861	K	AS PER THIS DWG.	.075	240/480	120/240	60	H-18969	NONE
X-343860	K	AS PER THIS DWG.	.040	220/440	110	25	H-18969	NONE
X-343859	K	AS PER THIS DWG.	.060	220/440	110	40	H-18969	NONE
X-343858	K	AS PER THIS DWG.	.075	240/480 220/440	120 110	60 50/60	45010-334-02	1497-N2



REFERENCE		DIMENSIONS APPLY BEFORE SURFACE TREATMENT (DIMENSIONS IN INCHES) TOLERANCES UNLESS OTHERWISE SPECIFIED .XX: ± .XXX: ± ANGLES: ±	DUAL VOLTAGE CONTROL TRANSFORMER 		MAC DOCUMENT THIS DRAWING IS THE PROPERTY OF THE ALLEN-BRADLEY CO. INC. AND MAY NOT BE COPIED, USED OR DISCLOSED FOR ANY PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY THE ALLEN-BRADLEY CO. INC.	
REVISION AUTHORIZATION 17 2075-96 18 2075C-96					LOCATION: MILWAUKEE, WISCONSIN U.S.A. DR. Lynn Mickelson DATE 5-4-99 CHKD. _____ DATE _____ APPD. _____ DATE _____	
			DWG SIZE B		SHEET 2 OF 2 X-343858-907	