

1756 ControlLogix Communication Modules Specifications

Standard ControlLogix Catalog Numbers 1756-CN2, 1756-CN2R, 1756-CNB, 1756-CNBR, 1756-CN2RK, 1756-DNB, 1756-DHRIO, 1756-DH485, 1756-EN2F, 1756-EN2T, 1756-EN2TR, 1756-EN3TR, 1756-EN2TSC, 1756-ENBT, 1756-EWEB, 1756-RIO, 1756-SYNCH, 1756-TIME

ControlLogix-XT Catalog Numbers 1756-CN2RXT, 1756-DHRIOXT, 1756-EN2TXT, 1756-EN2TRXT

| Topic | Page |
|---------------------------------|------|
| Additional Resources | 2 |
| New and Updated Information | 2 |
| Available Communication Modules | 2 |
| EtherNet/IP Network | 4 |
| Stratix Switches | 12 |
| ControlNet Network | 13 |
| DeviceNet Network | 21 |
| DH+ and Remote I/O Networks | 24 |
| DH-485 Network | 30 |
| SynchLink Communication | 32 |
| Time Synchronization | 34 |



Additional Resources

These documents contain additional information concerning related products from Rockwell Automation®.

| Resource | Description |
|--|---|
| EtherNet/IP Modules Installation Instructions, publication ENET-IN002 | Provides information on installing EtherNet/IP modules. |
| EtherNet/IP Secure Communication User Manual, publication ENET-UM003 | Provides information on system architecture, configuring secure communication, and diagnostics. |
| ControlNet Modules Installation Instructions, publication CNET-IN005 | Provides instructions for installing ControlNet modules. |
| ControlLogix® System User Manual, publication 1756-UM001 | Provides information on system architecture, configuring secure communication, and diagnostics. |
| DeviceNet Network Configuration User Manual, publication DNET-UM004 | Provides information on system architecture, configuring communication, and diagnostics. |
| ControlLogix DH-485 Communication Module User Manual, publication 1756-UM532 | Provides information on system architecture, configuring communication, and diagnostics. |
| ControlLogix Data Highway Plus-Remote I/O Communication Interface Module User Manual, publication 1756-UM514 | Provides information about programming, messaging, applying, and connecting the module. |
| ControlLogix SynchLink™ Module User Manual, publication 1756-UM521 | Provides information about topologies, configurations, planning, and installing a Synchlink module. |
| Industrial Automation Wiring and Grounding Guidelines, publication 1770-4.1 | Provides general guidelines for installing a Rockwell Automation industrial system. |
| Product Certifications website, http://www.ab.com | Provides declarations of conformity, certificates, and other certification details. |

You can view or download publications at <http://www.rockwellautomation.com/literature/>. To order paper copies of technical documentation, contact your local Allen-Bradley distributor or Rockwell Automation sales representative.

New and Updated Information

This table contains the changes made in this revision.

| Topic | Page |
|---|------|
| Added the 1756-TIME Time Synchronization module | 34 |

Available Communication Modules

| Network | Cat. No. | Description | Page |
|-------------|--------------|---|------|
| EtherNet/IP | 1756-EN2F | EtherNet/IP bridge, fiber, 256 Logix connections | 6 |
| | 1756-EN2T | EtherNet/IP bridge, copper, 256 Logix connections | 6 |
| | 1756-EN2TSC | EtherNet/IP secure communication module | 6 |
| | 1756-EN2TR | EtherNet/IP bridge, embedded switch, copper Supports as many as 8 axis of motion | 6 |
| | 1756-EN3TR | EtherNet/IP bridge, embedded switch, copper Supports as many as 128 axis of motion | 6 |
| | 1756-ENBT | EtherNet/IP bridge, copper, 128 Logix connections | 6 |
| | 1756-EWEB | Ethernet web server, 128 Logix connections, Class 3 messaging only | 6 |
| | 1756-EN2TXT | ControlLogix-XT™, EtherNet/IP bridge, copper, 256 Logix connections | 6 |
| | 1756-EN2TRXT | ControlLogix-XT EtherNet/IP bridge module with embedded switch | 6 |

| Network | Cat. No. | Description | Page |
|----------------------|--|---|------|
| ControlNet | 1756-CN2/B, 1756-CN2/C 1756-CN2R/B, 1756-CN2R/C 1756-CN2RK | ControlNet bridge, 128 Logix connections ⁽¹⁾ | 13 |
| | 1756-CNB, 1756-CNBR | ControlNet bridge, 64 connections; recommend using only 40 . . . 48 Logix connections for I/O | 13 |
| | 1756-CN2RXT | ControlLogix-XT, ControlNet bridge, 128 Logix connections ⁽¹⁾ | 17 |
| DeviceNet | 1756-DNB/E | DeviceNet bridge | 21 |
| Data Highway Plus™ | 1756-DHRIO | Data Highway Plus/Remote I/O module | 25 |
| | 1756-DHRIOXT | ControlLogix-XT, Data Highway Plus/Remote I/O module | 27 |
| Remote I/O | 1756-DHRIO | Data Highway Plus/Remote I/O module | 25 |
| | 1756-RIO/B | Remote I/O module | 25 |
| | 1756-DHRIOXT | ControlLogix-XT, Data Highway Plus/Remote I/O module | 27 |
| DH-485 module | 1756-DH485 | DH-485 module | 30 |
| SynchLink™ | 1756-SYNCH | SynchLink fiber-optic communication link | 32 |
| Time Synchronization | 1756-TIME | Time synchronization on different interfaces by using Global Positioning System (GPS) technology. | 34 |

(1) 128 connections are available for standard use. An additional three connections are reserved for redundant control.

Communication Connections

A ControlLogix system uses connections to establish communication links between devices. The types of connections include the following:

- Controller-to-local I/O modules or local communication modules
- Controller-to-remote I/O or remote communication modules
- Controller-to-remote I/O (rack-optimized) modules
- Produced and consumed tags
- Messages
- Controller access with the Studio 5000 environment
- Controller access with RSLinx® software for HMI or other applications

You indirectly determine the number of connections the controller uses by configuring the controller to communicate with other devices in the system. The limit of connections may ultimately reside in the communication module you use for the connection. If a message path routes through a communication module, the connection that is related to the message also counts towards the connection limit of that communication module.

EtherNet/IP Network



The Ethernet Industrial (EtherNet/IP) network protocol is an open industrial-networking standard that supports both real-time I/O messaging and message exchange. The EtherNet/IP network uses off-the-shelf Ethernet communication chips and physical media.

| If you need to | Select this interface |
|--|--|
| Control I/O modules and drives Act as an adapter for I/O on remote EtherNet/IP links Communicate with other EtherNet/IP devices (messages and HMI) Bridge EtherNet/IP links to route messages to devices on other networks | 1756-EN2F bridge 1756-EN2T bridge 1756-ENBT bridge |
| Support device level ring (DLR) and linear topologies | 1756-EN2TR redundant bridge 1756-EN3TR redundant bridge |
| Provide control in environments where temperatures range from -25...70 °C (-13...158 °F) | 1756-EN2TXT bridge |
| Support device level ring (DLR) and linear topologies Provide control in environments where temperatures range from -25...70 °C (-13...158 °F) | 1756-EN2TRXT redundant bridge |
| Secure access to a control system from within the plant network | 1756-EN2TSC bridge |
| Use an Internet browser to remotely access tags in a ControlLogix controller Communicate with other EtherNet/IP or generic Ethernet devices (messaging only; no I/O control) Bridge EtherNet/IP links to route messages to devices on other networks | 1756-EWEB web server |

EtherNet/IP Network Specifications

Table 1 - ControlLogix EtherNet/IP Connections Specifications

| Cat. No. | Connections | | CIP Unconnected Messages (backplane + Ethernet) |
|--------------|-------------|--------------------|---|
| | TCP | CIP ⁽¹⁾ | |
| 1756-ENBT | 64 | 128 | 64 + 64 |
| 1756-EN2F | 128 | 256 | 128 + 128 |
| 1756-EN2T | 128 | 256 | 128 + 128 |
| 1756-EN2TXT | 128 | 256 | 128 + 128 |
| 1756-EN2TR | 128 | 256 | 128 + 128 |
| 1756-EN2TRXT | 128 | 256 | 128 + 128 |
| 1756-EN2TSC | 128 | 256 | 128 + 128 |
| 1756-EN3TR | 128 | 256 | 128 + 128 |
| 1756-EWEB | 64 | 128 ⁽¹⁾ | 128 + 128 |

(1) CIP connections can be used for all explicit or all implicit applications. For example, a 1756-ENBT module has a total of 128 CIP connections that can be used for any combination of connections.

Table 2 - ControlLogix EtherNet/IP Data Specifications

| Cat. No. | Produced/Consumed Tags | | Socket Services | SNMP Support (password required) | Duplicate IP Detection (starting revision) |
|--------------|--|--|-----------------|----------------------------------|--|
| | Number of Multicast Tags, Max ⁽¹⁾ | Unicast Available in RSLogix 5000 Software | | | |
| 1756-ENBT | 32 | Version 16.03.00 or later | No | Yes | Revision 3.3 |
| 1756-EN2F | 32 | Version 16.03.00 or later | Yes | Yes | Revision 1.x |
| 1756-EN2T | 32 | Version 16.03.00 or later | Yes | Yes | Revision 1.x |
| 1756-EN2TXT | 32 | Version 16.03.00 or later | Yes | Yes | Revision 1.x |
| 1756-EN2TR | 32 | Version 17.01.02 or later | Yes | Yes | Revision 1.x |
| 1756-EN2TRXT | 32 | Version 20.01.00 or later | Yes | Yes | Revision 1.x |
| 1756-EN2TSC | 32 | Version 20.01.00 or later | No | Yes | Revision 1.x |
| 1756-EN3TR | 32 | Version 18.02.00 or later | Yes | Yes | Revision 3.x |
| 1756-EWEB | N/A | N/A | Yes | Yes | Revision 2.2 |

(1) Each controller can send a maximum of 32 produced tags to one single consuming controller. If these same tags are sent to multiple consumers, the maximum number is 31.

Table 3 - ControlLogix EtherNet/IP Packet Rates Specifications

| Cat. No. | Firmware Revision | RSLogix 5000 Software Version | RSLinx Software Version | Packet Rate Capacity (packets/second) ⁽²⁾ | | Support for Extended Environment ⁽³⁾ | Integrated Motion on the EtherNet/IP Network Axes |
|-----------|-------------------|----------------------------------|-------------------------|--|---------|---|---|
| | | | | I/O | HMI/MSG | | |
| 1756-ENBT | Any | 8.02.00 or later | 2.30 or later | 5000 | 900 | No | N/A |
| 1756-EN2F | 2.x | 15.02.00 or later | 2.51 or later | 10,000 | 2000 | No | N/A |
| | 3.6 or later | 18.02.00 or later ⁽¹⁾ | | 25,000 | | | Up to 4 axes supported ⁽⁴⁾ |
| 1756-EN2T | 2.x or earlier | 15.02.00 or later | 2.51 or later | 10,000 | 2000 | No | Up to 8 axes supported ⁽⁴⁾ |
| | 3.6 or later | 18.02.00 or later ⁽¹⁾ | | 25,000 ⁽⁴⁾ | | | Up to 8 axes supported ⁽⁴⁾ |

Table 3 - ControlLogix EtherNet/IP Packet Rates Specifications

| Cat. No. | Firmware Revision | RSLogix 5000 Software Version | RSLinx Software Version | Packet Rate Capacity (packets/second) ⁽²⁾ | | Support for Extended Environment ⁽³⁾ | Integrated Motion on the EtherNet/IP Network Axes |
|--------------|-------------------|----------------------------------|-------------------------|--|--|---|---|
| | | | | I/O | HMI/MSG | | |
| 1756-EN2TXT | 2.x | 15.02.00 or later | 2.51 or later | 10,000 | 2000 | Yes | N/A |
| | 3.6 or later | 18.02.00 or later ⁽¹⁾ | | 25,000 ⁽⁴⁾ | | | Up to 8 axes supported ⁽⁴⁾ |
| 1756-EN2TR | 2.x | 17.01.02 or later | 2.55 or later | 10,000 | 2000 | No | N/A |
| | 3.6 or later | 18.02.00 or later ⁽¹⁾ | 2.56 or later | 25,000 ⁽⁴⁾ | | | Up to 8 axes supported ⁽⁴⁾ |
| 1756-EN2TRXT | 5.028 or later | 20.01.00 or later | 2.56 or later | 25,000 ⁽⁴⁾ | 2000 | Yes | N/A |
| 1756-EN2TSC | 5.028 or later | 20.01.00 or later | 2.56 or later | 25,000 ⁽⁴⁾ | 930 with encryption 1800 without encryption | No | N/A |
| 1756-EN3TR | 3.6 or later | 18.02.00 or later ⁽¹⁾ | 2.56 or later | 25,000 ⁽⁴⁾ | 2000 | No | Up to 255 axes supported ⁽⁴⁾ |

(1) This version is required to use CIP Sync technology, Integrated Motion on the EtherNet/IP Network, or Exact Match keying.

(2) I/O numbers are maximums; they assume no HMI/MSG. HMI/MSG numbers are maximums, they assume no I/O. Packet rates vary depending on packet size. For more details, see Troubleshoot EtherNet/IP Application Technique, publication [ENET-AT003](#), and the EDS file for a specific catalog number.

(3) Module operates in a broad temperature spectrum, -20...70 °C (-4...158 °F), and meets ANSI/ISA-571.04-1985 Class G1, G2 and G3, as well as cULus, Class 1 Div 2, C-Tick, CE, ATEX Zone 2 and SIL 2 requirements for increased protection against salts, corrosives, moisture/condensation, humidity, and fungal growth.

(4) This value assumes the use of a 1756-L7x ControlLogix controller. For a 1756-L6x ControlLogix controller, see ControlLogix Controllers User Manual, publication [1756-UM001](#).

Table 4 - Technical Specifications - 1756 EtherNet/IP Modules

| Attribute | 1756-EN2F/C | 1756-EN2T/D, 1756-EN2TSC/B | 1756-EN2TR/C, 1756-EN3TR/B | 1756-ENBT/A | 1756-EWEB/B |
|--------------------------------|---|--|--|---|---|
| EtherNet/IP communication rate | 10/100 Mbps | | | | |
| Current draw @ 5.1V DC | 1.2 A | 1A | 1A | 700 mA | 700 mA |
| Current draw @ 24V DC | 3 mA | — | — | 3 mA | 3 mA |
| Voltage and current ratings | 5.1 V DC, 1.2A | — | — | — | — |
| Power dissipation | 6.2 W | 5.1 W | 5.1 W | 3.7 W | 3.7 W |
| Thermal dissipation | 21.28 BTU/hr | 17.4 BTU/hr | 17.4 BTU/hr | 12.6 BTU/hr | 12.6 BTU/hr |
| Isolation voltage | 30V (continuous), Basic Insulation Type, USB to Backplane Type tested at 980V AC for 60 s | 30V (continuous), Basic Insulation Type, Ethernet to Backplane, USB to Backplane, and USB to Ethernet ⁽³⁾ Type tested at 980V AC for 60 s | 30V (continuous), Basic Insulation Type, Ethernet to Backplane, USB to Backplane, and USB to Ethernet ⁽³⁾ Type tested at 980V AC for 60 s | 30V (continuous), basic insulation type, Ethernet network to backplane Type tested @ 707V DC for 60 s | 30V (continuous), basic insulation type, Ethernet network to backplane Type tested @ 707V DC for 60 s |
| Slot width | 1 | | | | |
| Module location | Chassis-based, any slot | | | | |
| Chassis | 1756-A4, 1756-A7, 1756-A10, 1756-A13, 1756-A17 | | | | |
| Power supply, standard | 1756-PA72, 1756-PA75, 1756-PB72, 1756-PB75, 1756-PC75, 1756-PH75 | | | | |
| Power supply, redundant | 1756-PA75R, 1756-PB75R, 1756-PSCA2 | | | | |
| Ethernet port | 1 Ethernet fiber | 1 Ethernet RJ45 Category 5 | 2 Ethernet RJ45 Category 5 | 1 Ethernet RJ45 Category 5 | |
| Ethernet cable | Multimode fiber, LC connector | 802.3 compliant shielded or unshielded twisted pair | 802.3 compliant shielded or unshielded twisted pair | 802.3 compliant shielded or unshielded twisted pair | 802.3 compliant shielded or unshielded twisted pair |

Table 4 - Technical Specifications - 1756 EtherNet/IP Modules

| Attribute | 1756-EN2F/C | 1756-EN2T/D, 1756-EN2TSC/B | 1756-EN2TR/C, 1756-EN3TR/B | 1756-ENBT/A | 1756-EWEB/B |
|--|---|---|---|-----------------------|-----------------------|
| USB port ⁽¹⁾ | USB 1.1, full speed (12 Mbps) | USB 1.1, full speed (12 Mbps) | USB 1.1, full speed (12 Mbps) | — | — |
| Wiring category ⁽²⁾ | 3 - on USB ports | 2 - on Ethernet ports 3 - on USB ports | 2 - on Ethernet ports 3 - on USB ports | 2 - on Ethernet ports | 2 - on Ethernet ports |
| North American temperature code | T4A | | | | |
| IEC temperature code | T4 | | | | |
| Enclosure type rating | None (open-style) | | | | |
| Transmitter launch power at Beginning of Life (BOL), min Allow -1 dB at End of Life (EOL) | -19 dBm into 62.5/125 μ m fiber, N/A = 0.275 -22.5 dBm into 50/125 μ m fiber, N/A = 0.20 | — | — | — | — |

- (1) The USB port is intended for temporary local programming purposes only and not intended for permanent connection. Do not use the USB port in hazardous locations.
- (2) Use this conductor category information for planning conductor routing as described in the system level installation manual. See the Industrial Automation Wiring and Grounding Guidelines, publication [1770-4.1](#).
- (3) Applies only to these modules/series: 1756-EN2T/D, 1756-EN2TSC/B, 1756-EN2TR/C, 1756-EN3TR/B.

Table 5 - Environmental Specifications - 1756 EtherNet/IP Modules

| Attribute | 1756-EN2F/B | 1756-EN2T/D, 1756-EN2TSC/B | 1756-EN2TR/C, 1756-EN3TR/B | 1756-ENBT/A, 1756-EWEB/B |
|---|--|-------------------------------|-------------------------------|-----------------------------|
| Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | 0...60 °C (32...140 °F) | | | |
| Temperature, surrounding air, max | 60 °C (140 °F) | | | |
| Temperature, storage IEC 60068-2-1 (Test Ab, Unpackaged Nonoperating Cold) IEC 60068-2-2 (Test Bb, Unpackaged Nonoperating Dry Heat) IEC 60068-2-14 (Test Na, Unpackaged Nonoperating Thermal Shock) | -40...85 °C (-40...185 °F) | | | |
| Relative humidity IEC 60068-2-30 (Test Db, Unpackaged damp heat) | 5...95% noncondensing | | | |
| Vibration IEC 60068-2-6 (Test Fc, Operating) | 2 g @ 10...500 Hz | | | |
| Shock, operating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g | | | |
| Shock, nonoperating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g | 30 g ⁽¹⁾ | 30 g ⁽¹⁾ | 50 g |
| Emission CISPR 11 (IEC 61000-6-4) | Class A | | | |
| ESD immunity IEC 61000-4-2 | 6 kV contact discharges 8 kV air discharges | | | |

Table 5 - Environmental Specifications - 1756 EtherNet/IP Modules (Continued)

| Attribute | 1756-EN2F/B | 1756-EN2T/D, 1756-EN2TSC/B | 1756-EN2TR/C, 1756-EN3TR/B | 1756-ENBT/A, 1756-EWEB/B |
|---|--|--|--|--|
| Radiated RF immunity IEC 61000-4-3 | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 3V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 3V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 3V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 1V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz |
| EFT/B immunity IEC 61000-4-4 | — | ±3 kV at 5 kHz on Ethernet ports ⁽¹⁾ | ±3 kV at 5 kHz on Ethernet ports ⁽¹⁾ | ±2 kV at 5 kHz on Ethernet ports |
| Surge transient immunity IEC 61000-4-5 | — | ±2 kV line-earth (CM) on Ethernet ports | ±2 kV line-earth (CM) on Ethernet ports | ±2 kV line-earth (CM) on Ethernet ports |
| Conducted RF immunity IEC 61000-4-6 | 10V rms with 1 kHz sine-wave 80% AM from 150 kHz...80 MHz | | | |

(1) Applies only to these modules/series: 1756-EN2T/D, 1756-EN2TSC/B, 1756-EN2TR/C, 1756-EN3TR/B.

Table 6 - Certifications - 1756 EtherNet/IP Modules

| Certification ⁽¹⁾ | 1756-EN2T/D | 1756-EN2F/C | 1756-EN2TSC/B | 1756-EN2TR/C, 1756-EN3TR/B | 1756-ENBT/A | 1756-EWEB/B |
|------------------------------|---|---|---------------|-------------------------------|--|--|
| c-UL-us | UL Listed Industrial Control Equipment, certified for US and Canada. See UL File E65584. UL Listed for Class I, Division 2 Group A,B,C,D Hazardous Locations, certified for U.S. and Canada. See UL File E194810. | | | | | |
| CSA | CSA Certified Process Control Equipment. See CSA File LR54689C. CSA Certified Process Control Equipment for Class I, Division 2 Group A,B,C,D Hazardous Locations. See CSA File LR69960C. | — | — | — | CSA Certified Process Control Equipment. See CSA File LR54689C. CSA Certified Process Control Equipment for Class I, Division 2 Group A,B,C,D Hazardous Locations. See CSA File LR69960C. | CSA Certified Process Control Equipment. See CSA File LR54689C. CSA Certified Process Control Equipment for Class I, Division 2 Group A,B,C,D Hazardous Locations. See CSA File LR69960C. |
| CE | European Union 2004/108/IEC EMC Directive, compliant with: EN 61326-1; Meas./Control/Lab., Industrial Requirements EN 61000-6-2; Industrial Immunity EN 61000-6-4; Industrial Emissions EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) | | | | | |
| RCM | Australian Radiocommunications Act, compliant with EN 61000-6-4; Industrial Emissions | | | | | |
| Ex | European Union 94/9/EC ATEX Directive, compliant with the following: EN 60079-15; Potentially Explosive Atmospheres, Protection "n" EN 60079-0; General Requirements II 3 G Ex nA IIC T4 Gc X DEMKO13ATEX1325026X (1756-EN2T/C only) | | | | | |
| FM | All modules except 1756-EN2TSC: FM Approved Equipment for use in Class I Division 2 Group A,B,C,D Hazardous Locations | | | | | |
| IECEx | — | IECEx System, compliant with: IEC 60079-15; Potentially Explosive Atmospheres, Protection "n" IEC 60079-0; General Requirements II 3 G Ex nA IIC T4 Gc IECEx UL 14.0008X | — | — | — | — |

Table 6 - Certifications - 1756 EtherNet/IP Modules

| Certification ⁽¹⁾ | 1756-EN2T/D | 1756-EN2F/C | 1756-EN2TSC/B | 1756-EN2TR/C, 1756-EN3TR/B | 1756-ENBT/A | 1756-EWEB/B |
|------------------------------|---|-------------|---------------|-------------------------------|-------------|-------------|
| KC | Korean Registration of Broadcasting and Communications Equipment, compliant with: Article 58-2 of Radio Waves Act, Clause 3 | | | | | |
| EAC | Russian Customs Union TR CU 020/2011 EMC Technical Regulation, compliant with: Russian Customs Union TR CU 004/2011 LV Technical Regulation, compliant with: | | | | | |
| EtherNet/IP | ODVA conformance tested to EtherNet/IP specifications | | | | | |

(1) When product is marked. See the Product Certification link at <http://www.ab.com> for Declarations of Conformity, Certificates, and other certification details.

Table 7 - Technical Specifications - 1756 EtherNet/IP-XT Modules

| Attribute | 1756-EN2TXT/D, 1756-EN2TRXT/C |
|----------------------------------|--|
| EtherNet/IP communication rate | 10/100 Mbps |
| Logix communication connections | 256 |
| TCP/IP communication connections | 128 |
| Current draw @ 5.1V DC | 1 A |
| Power dissipation | 5.1 W 17.4BTU/Hr |
| Thermal dissipation | 17.4 BTU/hr |
| Isolation voltage | 30V (continuous), Basic Insulation Type, Ethernet to Backplane, USB to Backplane, and USB to Ethernet ⁽¹⁾ |
| Slot width | 1 |
| Module location | Chassis-based, any slot |
| Chassis | 1756-A4LXT, 1756-A5XT, 1756-A7XT, 1756-A7LXT |
| Power supply, standard | 1756-PAXT, 1756-PBXT |
| Power supply, redundant | None |
| Ethernet port | 2 Ethernet RJ45 Category 5 |
| Ethernet cable | 802.3 compliant shielded or unshielded twisted pair |
| USB port ⁽²⁾ | USB 1.1, full speed (12 Mbps) |
| Wiring category ⁽³⁾ | 2 - on Ethernet ports 3 - on USB ports |
| North American temperature code | T4A |
| IEC temperature code | T4 |
| Enclosure type rating | None (open-style) |

(1) Applies only to these modules/series: 1756-EN2TXT/D, 1756-EN2TRXT/C.

(2) The USB port is intended for temporary local programming purposes only and not intended for permanent connection. Do not use the USB port in hazardous locations.

(3) Use this conductor category information for planning conductor routing as described in the system level installation manual. See the Industrial Automation Wiring and Grounding Guidelines, publication [1770-4.1](#).

Table 8 - Environmental Specifications - 1756 EtherNet/IP-XT Module

| Attribute | 1756-EN2TXT/D, 1756-EN2TRXT/C |
|--|--|
| Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | -25...70 °C (-13...158 °F) |
| Temperature, surrounding air, max | 70 °C (158 °F) |
| Temperature, storage IEC 60068-2-1 (Test Ab, Unpackaged Nonoperating Cold), IEC 60068-2-2 (Test Bb, Unpackaged Nonoperating Dry Heat) IEC 60068-2-14 (Test Na, Unpackaged Nonoperating Thermal Shock) | -40...85 °C (-40...185 °F) |
| Relative humidity IEC 60068-2-30 (Test Db, Unpackaged damp heat) | 5...95% noncondensing |
| Vibration IEC 60068-2-6 (Test Fc, Operating) | 2 g @ 10...500 Hz |
| Shock, operating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g |
| Shock, nonoperating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g |
| Emissions CISPR 11 (IEC 61000-6-4) | Class A |
| ESD immunity IEC 61000-4-2 | 6 kV contact discharges 8k V air discharges |
| Radiated RF immunity IEC 61000-4-3 | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 3V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz |
| EFT/B immunity IEC 61000-4-4 | ±3 kV at 5 kHz on Ethernet ports ⁽¹⁾ |
| Surge transient immunity IEC 61000-4-5 | ±2 kV line-earth (CM) on Ethernet ports |
| Conducted RF immunity IEC 61000-4-6 | 10V rms with 1 kHz sine-wave 80% AM from 150 kHz...80 MHz |

(1) Applies only to these modules/series: 1756-EN2TXT/D, 1756-EN2TRXT/C.

Table 9 - Certifications - 1756 EtherNet/IP-XT Module

| Certification ⁽¹⁾ | 1756-EN2TXT/D, 1756-EN2TRXT/C |
|------------------------------|--|
| c-UL-us | UL Listed Industrial Control Equipment, certified for US and Canada. See UL File E65584. UL Listed for Class I, Division 2 Group A,B,C,D Hazardous Locations, certified for U.S. and Canada. See UL File E194810. |
| CE | European Union 2004/108/IEC EMC Directive, compliant with the following: <ul style="list-style-type: none"> EN 61326-1; Meas./Control/Lab., Industrial Requirements EN 61000-6-2; Industrial Immunity EN 61000-6-4; Industrial Emissions EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) |
| RCM | Australian Radiocommunications Act, compliant with EN 61000-6-4; Industrial Emissions |
| Ex | European Union 94/9/EC ATEX Directive, compliant with the following: <ul style="list-style-type: none"> EN 60079-15; Potentially Explosive Atmospheres, Protection "n" EN 60079-0; General Requirements II 3 G Ex nA IIC T4 Gc X |
| KC | Korean Registration of Broadcasting and Communications Equipment, compliant with: Article 58-2 of Radio Waves Act, Clause 3 |
| EtherNet/IP | ODVA conformance tested to EtherNet/IP specifications |

(1) When product is marked. See the Product Certification link at <http://www.ab.com> for Declarations of Conformity, Certificates, and other certification details.

ENET Module Diagrams

Figure 1 - 1756-EN2T




Figure 2 - 1756-EN2TR, 1756-EN3TR





Figure 3 - 1756-EN2F

Accessories—Ethernet Network

| Cat. No. | Description | Specifications |
|----------------|---|--|
| 1585J-M8PBJM-x | Ethernet RJ45 patchcord x = 2 (2 m), 5 (5 m), or 10 (10 m) | 8-conductor, teal riser PVC cable (flex-rated cable also available) |
| 1585J-M8CC-H | RJ45 insulation displacement connector (IDC) | 0.128...0.325 mm ² (26...22 AWG), Cat. 6, IDC, no tool required |
| 1585J-M8CC-C | RJ45 crimp connector with boot, qty = 50 pieces | 0.128...0.205 mm ² (26...24 AWG), Cat. 5e, requires crimp tool for assembly |
| 1585A-JCRIMP | Crimp tool | — |
| 9300-RADES | Remote access dial-in kit | 56 Kbps modem connection to devices on an Ethernet network |

Stratix Switches

To effectively manage real-time control and information flow throughout the manufacturing and IT enterprise, Rockwell Automation offers a full portfolio of industrial Ethernet switches and media, including a line of Stratix switches integrated with Cisco technology. The Stratix line of switches includes modular managed, fixed managed, and unmanaged switches.

For detailed specifications for Stratix switches, see Stratix Ethernet Switch Specifications Technical Data, publication [1783-TD001](#).

ControlNet Network



The ControlNet network is an open, control network for real-time, high-throughput applications. The ControlNet network uses the Common Industrial Protocol (CIP) to combine the functionality of an I/O network and a peer-to-peer network providing high-speed performance for both functions. The ControlNet network gives you deterministic, repeatable transfers of all mission-critical control data in addition to supporting transfers of non-time-critical data. I/O updates and controller-to-controller interlocking always take precedence over program uploads and downloads, and messaging.

| If your application requires | Select one of these interfaces |
|--|--|
| 128 ControlNet connections per communication module | 1756-CN2/B 1756-CN2/C 1756-CN2R/B 1756-CN2R/C 1756-CN2RK/C 1756-CN2RXT/B 1756-CN2RXT/C |
| Control in environments where temperatures range from -25...70 °C (-13...158 °F) | 1756-CN2RXT/C |
| 40...48 ControlNet connections per communication module | 1756-CNB 1756-CNBR |

Connect to Other Devices via a ControlNet Network

The Studio 5000 environment supports a generic ControlNet module that allows connections to ControlNet nodes for which there is no specific support currently available in the programming software. A module configured as a generic ControlNet module communicates with the controller in the form of input, output, status, and configuration tags.

For example, use the generic module configuration to set up communication between a ControlLogix controller and a 1203-CN1 ControlNet communication module. Then use the CIP generic MSG instruction type to send and receive messages from the 1203-CN1 module.

Table 10 - Technical Specifications - 1756 ControlNet Modules

| Attribute | 1756-CN2/C | 1756-CN2R/C, 1756-CN2RK/C | 1756-CNB/E | 1756-CNBR/E |
|---------------------------------|--------------------|---------------------------|-------------|-------------|
| Configuration | Standard | Redundant | Standard | Redundant |
| ControlNet communication rate | 5 Mbps | | | |
| Logix communication connections | 128 | | 40...48 | |
| Connections supported, max | 131 ⁽³⁾ | | 64 | |
| Number of nodes, max | 99 | | | |
| Current draw @ 5.1V DC | 1100 mA | 1300 mA | 970 mA | |
| Current draw @ 24V DC | 3 mA | | 1.7 mA | |
| Power dissipation | 5.6 W | 6.7 W | 5.1 W | |
| Thermal dissipation | 19.1 BTU/Hr | 22.9 BTU/hr | 17.4 BTU/hr | |

Table 10 - Technical Specifications - 1756 ControlNet Modules (Continued)

| Attribute | 1756-CN2/C | 1756-CN2R/C, 1756-CN2RK/C | 1756-CNBR/E | 1756-CNBR/E |
|---------------------------------|---|---------------------------|---|--------------------|
| Isolation voltage | Standard: 30V (continuous), basic insulation type, ControlNet network to backplane Redundant: 30V (continuous), basic insulation type, ControlNet A/B to backplane, and ControlNet A to ControlNet B USB to backplane and USB to ControlNet No isolation between NAP or USB and backplane Type tested at 500V AC for 60 s | | | |
| Weight, approx. | 0.26 kg (0.57 lb) | 0.293 kg (0.64 lb) | 0.26 kg (0.57 lb) | 0.293 kg (0.64 lb) |
| Slot width | 1 | | | |
| Module location | Chassis-based, any slot | | | |
| Chassis | 1756-A4, 1756-A7, 1756-A10, 1756-A13, 1756-A17 | | | |
| Power supply, standard | 1756-PA72/C, 1756-PA75/B, 1756-PB72/C, 1756-PB75/B, 1756-PC75/B, 1756-PH75/B | | | |
| Power supply, redundant | 1756-PA75R, 1756-PB75R, 1756-PSCA2 | | | |
| ControlNet port | 1 ControlNet BNC | 2 ControlNet BNC | 1 ControlNet BNC | 2 ControlNet BNC |
| ControlNet cable | 1786-RG6 quad shield RG6 coaxial cable | | | |
| USB port ⁽¹⁾ | USB 1.1, full speed (12 Mbps) | | — | — |
| NAP port | — | — | 1 NAP RJ45 | 1 NAP RJ45 |
| NAP cable | — | — | 1786-CP | |
| Wiring category ⁽²⁾ | 1 - on ControlNet ports 3 - on USB ports | | 1 - on ControlNet ports 3 - on NAP ports | |
| North American temperature code | T4A | | | |
| IEC temperature code | T4 | | | |
| Enclosure type rating | None (open-style) | | | |

(1) The USB port is intended for temporary local programming purposes only and not intended for permanent connection. Do not use the USB port in hazardous locations.

(2) Use this conductor category information for planning conductor routing as described in the system level installation manual. See the Industrial Automation Wiring and Grounding Guidelines, publication [1770-4.1](#).

(3) 128 connections are available for standard use. An additional three connections are reserved for redundant control.

Table 11 - Environmental Specifications - 1756 ControlNet Modules

| Attribute | 1756-CN2/C, 1756-CN2R/C, 1756-CN2RK/C | 1756-CNB/E, 1756-CNBR/E |
|---|--|----------------------------|
| Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | 0...60 °C (32...140 °F) | |
| Temperature, surrounding air, max | 60 °C (140 °F) | |
| Temperature, storage IEC 60068-2-1 (Test Ab, Unpackaged Nonoperating Cold) IEC 60068-2-2 (Test Bb, Unpackaged Nonoperating Dry Heat) IEC 60068-2-14 (Test Na, Unpackaged Nonoperating Thermal Shock) | -40...85 °C (-40...185 °F) | |
| Relative humidity IEC 60068-2-30 (Test Db, Unpackaged Damp Heat) | 5...95% noncondensing | |
| Vibration IEC 60068-2-6 (Test Fc, Operating) | 2 g @ 10...500 Hz | |
| Shock, operating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g | |
| Shock, nonoperating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g | 50 g |
| Emissions CISPR 11 (IEC 61000-6-4) | Class A | |
| ESD immunity IEC 61000-4-2 | 6 kV contact discharges 8 kV air discharges | |
| Radiated RF immunity IEC 61000-4-3 | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 3V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz | |
| EFT/B immunity IEC 61000-4-4 | ±3 kV at 5 kHz on ControlNet ports | |
| Surge transient immunity IEC 61000-4-5 | ±2 kV line-earth (CM) on ControlNet ports | |
| Conducted RF immunity IEC 61000-4-6 | 10V rms with 1 kHz sine-wave 80% AM from 150 kHz...80 MHz | |

Table 12 - Certifications - 1756 ControlNet Modules

| Certification ⁽¹⁾ | 1756-CN2R/B, 1756-CNB/E, 1756-CNBR/E | 1756-CN2/C, 1756-CN2R/C, 1756-CN2RK/C |
|------------------------------|--|---------------------------------------|
| c-UL-us | UL Listed Industrial Control Equipment, certified for US and Canada. See UL File E65584. UL Listed for Class I, Division 2 Group A,B,C,D Hazardous Locations, certified for U.S. and Canada. See UL File E194810. | |
| CSA | CSA Certified Process Control Equipment. See CSA File LR54689C. CSA Certified Process Control Equipment for Class I, Division 2 Group A,B,C,D Hazardous Locations. See CSA File LR69960C. | NA |
| CE | European Union 2004/108/IEC EMC Directive, compliant with the following: <ul style="list-style-type: none"> • EN 61326-1; Meas./Control/Lab., Industrial Requirements • EN 61000-6-2; Industrial Immunity • EN 61000-6-4; Industrial Emissions • EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) | |
| RCM | Australian Radiocommunications Act, compliant with: EN 61000-6-4; Industrial Emissions | |
| Ex | European Union 94/9/EC ATEX Directive, compliant with the following: <ul style="list-style-type: none"> • EN 60079-15; Potentially Explosive Atmospheres, Protection “n” • EN 60079-0; General Requirements • II 3 G Ex nA IIC T4 Gc X | |
| KC | Korean Registration of Broadcasting and Communications Equipment, compliant with: Article 58-2 of Radio Waves Act, Clause 3 | |
| FM | FM Approved Equipment for use in Class I Division 2 Group A,B,C,D Hazardous Locations | |
| CI | ControlNet International conformance tested to ControlNet specifications | |

(1) When product is marked. See the Product Certification link at <http://www.ab.com> for Declarations of Conformity, Certificates, and other certification details.

Table 13 - Technical Specifications - 1756 ControlNet-XT Module

| Attribute | 1756-CN2RXT/C |
|---------------------------------|--|
| Configuration | Redundant |
| ControlNet communication rate | 5 Mbps |
| Logix communication connections | 128 |
| Connections supported, max | 131 ⁽³⁾ |
| Number of nodes, max | 99 |
| Current draw @ 5.1V DC | 1300 mA |
| Current draw @ 24V DC | 3 mA |
| Voltage and current ratings | 5.1V DC, 1.3A |
| Power dissipation | 6.6W 22.5 BTU/Hr |
| Thermal dissipation | 22.9 BTU/hr |
| Isolation voltage | 30V (continuous), Basic Insulation Type, ControlNet A/B to Backplane, ControlNet A to ControlNet B, USB to ControlNet A/B, and USB to Backplane Type tested at 500V AC for 60 s |
| Weight, approx. | 0.293 kg (0.64 lb) |
| Slot width | 1 |
| Module location | Chassis-based, any slot |
| Chassis | 1756-A4LXT, 1756-A5XT, 1756-A7XT, 1756-A7LXT |
| Power supply, standard | 1756-PAXT, 1756-PBXT |
| Power supply, redundant | None |
| ControlNet port | 2 ControlNet BNC |
| ControlNet cable | 1786-RG6 quad-shield RG6 coaxial cable |
| USB port ⁽¹⁾ | USB 1.1, full speed (12 Mbps) |
| Wiring category ⁽²⁾ | 1 - on ControlNet ports 3 - on USB port |
| North American temperature code | T4A |
| IEC temperature code | T4 |
| Enclosure type rating | None (open-style) |

(1) The USB port is intended for temporary local programming purposes only and not intended for permanent connection. Do not use the USB port in hazardous locations.

(2) Use this conductor category information for planning conductor routing as described in the system level installation manual. See the Industrial Automation Wiring and Grounding Guidelines, publication [1770-4.1](#).

(3) There are 128 connections are available for standard use. An additional 3 connections are reserved for redundant control.

Table 14 - Environmental Specifications - 1756 ControlNet-XT Module

| Attribute | 1756-CN2RXT/C |
|---|--|
| Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | -25...70 °C (-13...158 °F) |
| Temperature, surrounding air, max | 70 °C (158 °F) |
| Temperature, storage IEC 60068-2-1 (Test Ab, Unpackaged Nonoperating Cold) IEC 60068-2-2 (Test Bb, Unpackaged Nonoperating Dry Heat) IEC 60068-2-14 (Test Na, Unpackaged Nonoperating Thermal Shock) | -40...85 °C (-40...185 °F) |
| Relative humidity IEC 60068-2-30 (Test Db, Unpackaged Damp Heat) | 5...95% noncondensing |
| Vibration IEC 60068-2-6 (Test Fc, Operating) | 2 g @ 10...500 Hz |
| Shock, operating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g |
| Shock, nonoperating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 1756-CN2RXT/C, 30 g 1756-CN2RXT/B, 50 g |
| Emissions CISPR 11 (IEC 61000-6-4) | Class A |
| ESD immunity IEC 61000-4-2 | 6 kV contact discharges 8 kV air discharges |
| Radiated RF immunity IEC 61000-4-3 | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 3V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz |
| EFT/B immunity IEC 61000-4-4 | ±3 kV at 5 kHz on ControlNet ports |
| Surge transient immunity IEC 61000-4-5 | ±2 kV line-earth (CM) on ControlNet port |
| Conducted RF immunity IEC 61000-4-6 | 10V rms with 1 kHz sine-wave 80% AM from 150 kHz...80 MHz |

Table 15 - Certifications - 1756 ControlNet-XT Module

| Certification ⁽¹⁾ | 1756-CN2RXT/C |
|------------------------------|--|
| c-UL-us | UL Listed Industrial Control Equipment, certified for US and Canada. See UL File E65584. UL Listed for Class I, Division 2 Group A,B,C,D Hazardous Locations, certified for U.S. and Canada. See UL File E194810. |
| CE | European Union 2004/108/IEC EMC Directive, compliant with the following: <ul style="list-style-type: none"> EN 61326-1; Meas./Control/Lab., Industrial Requirements EN 61000-6-2; Industrial Immunity EN 61000-6-4; Industrial Emissions EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) |
| RCM | Australian Radiocommunications Act, compliant with EN 61000-6-4; Industrial Emissions |
| Ex | European Union 94/9/EC ATEX Directive, compliant with the following: <ul style="list-style-type: none"> EN 60079-15; Potentially Explosive Atmospheres, Protection "n" EN 60079-0; General Requirements II 3 G Ex nA IIC T4 Gc X |
| KC | Korean Registration of Broadcasting and Communications Equipment, compliant with: Article 58-2 of Radio Waves Act, Clause 3 |
| CI | ControlNet International conformance tested to ControlNet specifications |

(1) When product is marked. See the Product Certification link at <http://www.ab.com> for Declarations of Conformity, Certificates, and other certification details.

CNET Module Diagrams



Figure 4 - 1756-CN2

Figure 5 - 1756-CN2R



Accessories—ControlNet Network

| Cat. No. | Description |
|------------------|--|
| Taps | |
| 1786-TCT2BD1 | T-tap straight IP67 rated |
| 1786-TPR | T-tap right angle |
| 1786-TPS | T-tap straight |
| 1786-TPYR | Y-tap right angle |
| 1786-TPYS | Y-tap straight |
| Cables | |
| 1786-CP | Programming cable to ControlNet RJ45 port |
| 1786-RG6 | ControlNet network, shield high-flex cable |
| 1756-RG6F | ControlNet network, quad-shield high-flex coax cable |
| Other | |
| 1786-TNCLXT4 | ControlNet IP67 termination resistor |
| 1786-XT | ControlNet termination resistor |
| Repeaters | |
| 1786-RPA | ControlNet modular repeater adapter |
| 1786-RPCD | ControlNet coaxial hub repeater |
| 1786-RPFRL | ControlNet fiber ring repeater, long distance |
| 1786-RPFRXL | ControlNet fiber ring repeater, extra long distance |
| 1786-RPFS | ControlNet fiber repeater, short distance |
| 1786-RPFM | ControlNet fiber repeater, medium distance |

For more information, see ControlNet Media System Components List, publication [AG-PA002](#).



DeviceNet Network

The DeviceNet network is open, providing connections between simple industrial devices, such as sensors and actuators, and higher-level devices, such as controllers and computers. The DeviceNet network uses the Common Industrial Protocol (CIP) to control, configure, and collect data for industrial devices

Table 16 - Technical Specifications - 1756-DNB DeviceNet Module

| Attribute | 1756-DNB/E |
|---------------------------------|--|
| DeviceNet communication rate | 125 Kbps (500 m max) 250 Kbps (250 m max) 500 Kbps (100 m max) |
| Number of nodes, max | 64 |
| Current draw @ 5.1V DC | 400 mA |
| Current draw @ 24V DC | 0 mA |
| DeviceNet current draw @ 24V DC | 60 mA |
| DeviceNet voltage range | 11...25V DC CL 2/SELV |
| Power dissipation | 3.5 W |
| Thermal dissipation | 11.9 BTU/hr |
| Isolation voltage | 50V (continuous), basic insulation type, DeviceNet network to backplane Type tested at 853V AC for 60 s No isolation between USB and backplane |
| Slot width | 1 |
| Module location | Chassis-based, any slot |
| Chassis | 1756-A4, 1756-A7, 1756-A10, 1756-A13, 1756-A17 |
| Power supply, standard | 1756-PA72/C, 1756-PA75/B, 1756-PB72/C, 1756-PB75/B, 1756-PC75/B, 1756-PH75/B |
| Power supply, redundant | 1756-PA75R, 1756-PB75R, 1756-PSCA2 |
| DeviceNet power | To comply with the CE low voltage directive (LVD), the DeviceNet network must be powered from a source compliant with the safety extra low voltage (SELV) or protected extra low voltage (PELV). To comply with UL restrictions, the DeviceNet network must be powered from a source compliant with Class 2 or limited voltage/current. |
| DeviceNet port | 1 DeviceNet open-style 5- or 10-pin linear plug |
| DeviceNet connector torque | 0.56...0.79 N·m (5...7 lb·in) |
| USB port ⁽¹⁾ | USB 2.0, full speed (12 Mbps) |
| Wiring category ⁽²⁾ | 1 - On DeviceNet ports 3 - On USB ports |
| North American temperature code | T4A |
| IEC temperature code | T4 |
| Enclosure type rating | None (open-style) |

(1) The USB port is intended for temporary local programming purposes only and not intended for permanent connection. Do not use the USB port in hazardous locations.

(2) Use this conductor category information for planning conductor routing as described in the system level installation manual. See the Industrial Automation Wiring and Grounding Guidelines, publication [1770-4.1](#). Refer to the DeviceNet Media Design and Planning Guide, publication [DNET-UM072](#), for information specific to your DeviceNet network.

Table 17 - Environmental Specifications - 1756-DNB DeviceNet Module

| Attribute | 1756-DNB/E |
|---|--|
| Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | 0...60 °C (32...140 °F) |
| Temperature, surrounding air, max | 60 °C (140 °F) |
| Temperature, storage IEC 60068-2-1 (Test Ab, Unpackaged Nonoperating Cold) IEC 60068-2-2 (Test Bb, Unpackaged Nonoperating Dry Heat) IEC 60068-2-14 (Test Na, Unpackaged Nonoperating Thermal Shock) | -40...85 °C (-40...185 °F) |
| Relative humidity IEC 60068-2-30 (Test Db, Unpackaged Damp Heat) | 5...95% noncondensing |
| Vibration IEC 60068-2-6 (Test Fc, Operating) | 2 g @ 10...500 Hz |
| Shock, operating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g |
| Shock, nonoperating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 50 g |
| Emissions CISPR 11 (IEC 61000-6-4): | Class A |
| ESD immunity IEC 61000-4-2 | 6 kV contact discharges 8 kV air discharges |
| Radiated RF immunity IEC 61000-4-3 | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 3V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz |
| EFT/B immunity IEC 61000-4-4 | ±3 kV at 5 kHz on DeviceNet ports |
| Surge transient immunity IEC 61000-4-5 | ±2 kV line-earth (CM) on DeviceNet ports |
| Conducted RF immunity IEC 61000-4-6 | 10V rms with 1 kHz sine-wave 80% AM from 150 kHz...80 MHz |

Table 18 - Certifications - 1756-DNB DeviceNet Module

| Certification ⁽¹⁾ | 1756-DNB/E |
|------------------------------|--|
| c-UL-us | UL Listed Industrial Control Equipment, certified for US and Canada. See UL File E65584. UL Listed for Class I, Division 2 Group A,B,C,D Hazardous Locations, certified for U.S. and Canada. See UL File E194810. |
| CSA | CSA Certified Process Control Equipment. See CSA File LR54689C. CSA Certified Process Control Equipment for Class I, Division 2 Group A,B,C,D Hazardous Locations. See CSA File LR69960C. |
| CE | European Union 2004/108/IEC EMC Directive, compliant with the following: <ul style="list-style-type: none"> EN 61326-1; Meas./Control/Lab., Industrial Requirements EN 61000-6-2; Industrial Immunity EN 61000-6-4; Industrial Emissions EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) |
| RCM | Australian Radiocommunications Act, compliant with EN 61000-6-4; Industrial Emissions |
| Ex | European Union 94/9/EC ATEX Directive, compliant with the following: <ul style="list-style-type: none"> EN 60079-15; Potentially Explosive Atmospheres, Protection “n” EN 60079-0; General Requirements II 3 G Ex nA IIC T4 Gc X |
| FM | FM Approved Equipment for use in Class I Division 2 Group A,B,C,D Hazardous Locations |
| KC | Korean Registration of Broadcasting and Communications Equipment, compliant with: Article 58-2 of Radio Waves Act, Clause 3 |
| DeviceNet | ODVA conformance tested to DeviceNet specifications |

(1) When product is marked. See the Product Certification link at <http://www.ab.com> for Declarations of Conformity, Certificates, and other certification details.

Accessories—DeviceNet Network

| Cat. No. | Description |
|---------------------------|---|
| KwikLink™ Lite flat media | KwikLink Lite flat media is a newer, ODVA-approved solution for wiring DeviceNet networks. Drop-lines for connecting nodes are added by using the KwikLink Lite two-piece connectors. This cable system supports the intermixing of DeviceNet cable types (thin-round with flat). All of the KwikLink Lite connectors provide insulation displacement technology with reduced assembly time. |
| KwikLink flat media | The KwikLink flat media system provides a modular cabling method with its flat four-wire cable and Insulation Displacement Connectors (IDCs). The KwikLink system allows nodes to be added to the network without severing the trunkline. Cutting or stripping of the trunkline is eliminated, as is the need for predetermined cable lengths. |
| Round media | Round trunk cable is available in bulk spools or as pre-molded cordsets or patchcords in varying lengths. A wide variety of rugged, durable DeviceNet components is available for use in round trunk systems. Stainless steel versions of round cable system components are also available: <ul style="list-style-type: none"> Thick-trunk round media systems use thick cable for maximum DeviceNet trunk line length. Round media thin-trunk systems use thin cable to reduce maximum trunk line distances with a more compact and cost-effective installation for some applications. Thin-cable outer jacket material is TPE for additional chemical resistance. |

For more information on selecting DeviceNet media, see the NetLinx™ Selection Guide, publication [NETS-SG001](#).

DH+ and Remote I/O Networks




The Data Highway Plus network supports messaging between devices. The remote I/O link connects to remote I/O chassis and other intelligent devices.

The 1756-DHRIO module supports messaging between devices on DH+™ networks. The remote I/O functionality enables the module to act as a scanner for transferring digital and block-transfer data to and from remote I/O devices.

The 1756-RIO module can act as a scanner or adapter on a remote I/O network. In addition to digital and block-transfer data, the 1756-RIO module transfers analog and specialty data without message instructions.

Example Configuration—DH+ Network



Example Configuration—Remote I/O Network




Table 19 - Technical Specifications - 1756 DH+ and Remote I/O Modules

| Attribute | 1756-DHRIO/E | 1756-RIO/B |
|---------------------------------|--|--|
| Communication rate | 57.6 Kbps, 115.2 Kbps, 230.4 Kbps | |
| Remote I/O communication | Remote I/O scanner only 32 logical rack connections per remote I/O channel 16 block-transfer connections per remote I/O channel | Remote I/O scanner or adapter 32 physical racks (0...76), any combination of rack size and block transfers |
| Connections supported, max | 32 | 10 scheduled I/O |
| Current draw @ 5.1V DC | 850 mA | 450 mA |
| Current draw @ 24V DC | 1.7 mA | 5 mA |
| Power dissipation | 4.5 W | 2.5 W |
| Thermal dissipation | 15.4 BTU/hr | 8.5 BTU/hr |
| Isolation voltage | 30V (continuous), basic insulation type, DHRIO A/B to backplane, and DHRIO A/programming port to DHRIO B No isolation between DHRIO A and Programming port Type tested at 877V DC for 60 s | 50V (continuous), basic insulation type, RIO communication lines to backplane Type tested at 500V AC for 60 s |
| Slot width | 1 | |
| Module location | Chassis-based, any slot | |
| Chassis | 1756-A4, 1756-A7, 1756-A10, 1756-A13, 1756-A17 | |
| Power supply, standard | 1756-PA72/C, 1756-PA75/B, 1756-PB72/C, 1756-PB75/B, 1756-PC75/B, 1756-PH75/B | |
| Power supply, redundant | 1756-PA75R, 1756-PB75R, 1756-PSCA2 | |
| Ports | 2, individually selectable for DH+ or remote I/O | 1 for remote I/O |
| Screw terminal torque | — | 0.5...0.6 N•m (5...7 lb•in) |
| Wire size | 0.519 mm ² (20 AWG) Belden 9463 copper twinaxial | |
| Wiring category ⁽¹⁾ | 2 - on DHRIO ports 3 - on local programming port | 2 - on RIO ports |
| North American temperature code | T4A | |
| IEC temperature code | T4 | — |
| Enclosure type rating | None (open-style) | |

(1) Use this conductor category information for planning conductor routing as described in the system level installation manual. See the Industrial Automation Wiring and Grounding Guidelines, publication [1770-4.1](#).

Table 20 - Environmental Specifications - 1756 DH+ and Remote I/O Modules

| Attribute | 1756-DHRIO/E | 1756-RIO/B |
|---|----------------------------|------------|
| Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | 0...60 °C (32...140 °F) | |
| Temperature, surrounding air, max | 60 °C (140 °F) | |
| Temperature, storage IEC 60068-2-1 (Test Ab, Unpackaged Nonoperating Cold) IEC 60068-2-2 (Test Bb, Unpackaged Nonoperating Dry Heat) IEC 60068-2-14 (Test Na, Unpackaged Nonoperating Thermal Shock) | -40...85 °C (-40...185 °F) | |
| Relative humidity IEC 60068-2-30 (Test Db, Unpackaged Damp Heat) | 5...95% noncondensing | |

Table 20 - Environmental Specifications - 1756 DH+ and Remote I/O Modules (Continued)

| Attribute | 1756-DHRIO/E | 1756-RIO/B |
|---|--|-----------------|
| Vibration IEC 60068-2-6 (Test Fc, Operating) | 2 g @ 10...500 Hz | |
| Shock, operating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g | |
| Shock, nonoperating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 50 g | |
| Emissions CISPR 11 (IEC 61000-6-4) | Class A | |
| ESD immunity IEC 61000-4-2 | 6 kV contact discharges 8 kV air discharges | |
| Radiated RF immunity IEC 61000-4-3 | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 3V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz | |
| EFT/B immunity IEC 61000-4-4 | ± 2 kV at 5 kHz | ± 2 kV at 5 kHz |
| Surge transient immunity IEC 61000-4-5 | ± 2 kV line-earth (CM) | |
| Conducted RF immunity IEC 61000-4-6 | 10V rms with 1 kHz sine-wave 80% AM from 150 kHz...80 MHz | |

Table 21 - Certifications - 1756 DH+ and Remote I/O Modules

| Certification ⁽¹⁾ | 1756-DHRIO/E | 1756-RIO/B |
|------------------------------|--|------------|
| c-UL-us | UL Listed Industrial Control Equipment, certified for US and Canada. See UL File E65584. UL Listed for Class I, Division 2 Group A,B,C,D Hazardous Locations, certified for U.S. and Canada. See UL File E194810. | |
| CSA | CSA Certified Process Control Equipment. See CSA File LR54689C. CSA Certified Process Control Equipment for Class I, Division 2 Group A,B,C,D Hazardous Locations. See CSA File LR69960C. | — |
| CE | European Union 2004/108/IEC EMC Directive, compliant with the following: <ul style="list-style-type: none"> • EN 61326-1; Meas./Control/Lab., Industrial Requirements • EN 61000-6-2; Industrial Immunity • EN 61000-6-4; Industrial Emissions • EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) | |
| RCM | Australian Radiocommunications Act, compliant with EN 61000-6-4; Industrial Emissions | |
| Ex | European Union 94/9/EC ATEX Directive, compliant with the following: <ul style="list-style-type: none"> • EN 60079-15; Potentially Explosive Atmospheres, Protection "n" • EN 60079-0; General Requirements II 3 G Ex nA IIC T4 Gc X | — |
| KC | Korean Registration of Broadcasting and Communications Equipment, compliant with: Article 58-2 of Radio Waves Act, Clause 3 | |

(1) When product is marked. See the Product Certification link at <http://www.ab.com> for Declarations of Conformity, Certificates, and other certification details.

Table 22 - Technical Specifications - 1756 DH+ and Remote I/O XT Module

| Attribute | 1756-DHRIOXT/E |
|--------------------------------------|--|
| Communication rate | 57.6 Kbps, 115.2 Kbps, 230.4 Kbps |
| DH+ communication connections | 32 DH+ messages per DH+ module |
| Remote I/O communication connections | Remote I/O scanner only 32 logical rack connections per remote I/O channel 16 block-transfer connections per remote I/O channel |
| Connections supported, max | 32 |
| Current draw @ 5.1V DC | 850 mA |
| Current draw @ 24V DC | 1.7 mA |
| Power dissipation | 4.5 W |
| Thermal dissipation | 15.4 BTU/hr |
| Isolation voltage | 30V (continuous), basic insulation type, DHRIO A/B to backplane, and DHRIO A/programming port to DHRIO B No Isolation between DHRIO A and Programming port Type tested at 853V AC for 60 s |
| Slot width | 1 |
| Module location | Chassis-based, any slot |
| Chassis | 1756-A4LXT, 1756-A5XT, 1756-A7XT, 1756-A7LXT |
| Power supply, standard | 1756-PBXT |
| Power supply, redundant | None |
| Ports | 2, individually selectable for DH+ or remote I/O |
| Screw terminal torque | 0.5...0.6 N•m (5...7 lb•in) |
| Wire size | 0.519 mm ² (20 AWG) Belden 9463 copper twinaxial |
| Wiring category ⁽¹⁾ | 2 - on DHRIO ports 3 - on local programming port |
| North American temperature code | T4A |
| IEC temperature code | T4 |
| Enclosure type rating | None (open-style) |

(1) Use this conductor category information for planning conductor routing as described in the system level installation manual. See the Industrial Automation Wiring and Grounding Guidelines, publication [1770-4.1](#).

Table 23 - Environmental Specifications - 1756 DH+ and Remote I/O XT Module

| Attribute | 1756-DHRIOXT |
|---|--|
| Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | -25...70 °C (-13...158 °F) |
| Temperature, surrounding air, max | 70 °C (158 °F) |
| Temperature, storage IEC 60068-2-1 (Test Ab, Unpackaged Nonoperating Cold) IEC 60068-2-2 (Test Bb, Unpackaged Nonoperating Dry Heat) IEC 60068-2-14 (Test Na, Unpackaged Nonoperating Thermal Shock) | -40...85 °C (-40...185 °F) |
| Relative humidity IEC 60068-2-30 (Test Db, Unpackaged Damp Heat) | 5...95% noncondensing |
| Vibration IEC 60068-2-6 (Test Fc, Operating) | 2 g @ 10...500 Hz |
| Shock, operating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g |
| Shock, nonoperating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 50 g |
| Emissions CISPR 11 (IEC 61000-6-4) | Class A |
| ESD immunity IEC 61000-4-2 | 6 kV contact discharges 8 kV air discharges |
| Radiated RF immunity IEC 61000-4-3 | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 1890 MHz 3V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz |
| EFT/B immunity IEC 61000-4-4 | ±2 kV at 5 kHz on DHRIO ports |
| Surge transient immunity IEC 61000-4-5 | ±2 kV line-earth (CM) on DHRIO ports |
| Conducted RF immunity IEC 61000-4-6 | 10V rms with 1 kHz sine-wave 80% AM from 150 kHz...80 MHz |

Table 24 - Certifications - 1756 DH+ and Remote I/O XT Module

| Certification ⁽¹⁾ | 1756-DHRIOXT |
|------------------------------|--|
| c-UL-us | UL Listed Industrial Control Equipment, certified for US and Canada. See UL File E65584. UL Listed for Class I, Division 2 Group A,B,C,D Hazardous Locations, certified for U.S. and Canada. See UL File E194810. |
| CE | European Union 2004/108/IEC EMC Directive, compliant with the following: <ul style="list-style-type: none"> • EN 61326-1; Meas./Control/Lab., Industrial Requirements • EN 61000-6-2; Industrial Immunity • EN 61000-6-4; Industrial Emissions • EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) |
| RCM | Australian Radiocommunications Act, compliant with EN 61000-6-4; Industrial Emissions |
| Ex | European Union 94/9/EC ATEX Directive, compliant with the following: <ul style="list-style-type: none"> • EN 60079-15; Potentially Explosive Atmospheres, Protection "n" • EN 60079-0; General Requirements II 3 G Ex nA IIC T4 Gc X |
| KC | Korean Registration of Broadcasting and Communications Equipment, compliant with: Article 58-2 of Radio Waves Act, Clause 3 |

(1) When product is marked. See the Product Certification link at <http://www.ab.com> for Declarations of Conformity, Certificates, and other certification details.

Accessories—DH+ and Remote I/O Networks

| Cat. No. | Description | Specifications |
|-------------|--|---|
| 1770-CD | Cable to connect communication module to DH+ network | Belden 9463 twinaxial |
| 9300-RADKIT | Remote access dial-in kit | 56 Kbps modem connection to devices on a DH+ network, including the following: <ul style="list-style-type: none"> • Preconfigured modem • Communication module • DIN rail mounting hardware • Associated cables |

DH-485 Network

On the DH-485 network, the controller can send and receive messages to and from other controllers on the network. The DH-485 connection does support remote programming and monitoring via the Studio 5000 environment. Excessive traffic over a DH-485 connection can adversely affect overall performance and can lead to timeouts and loss in the Studio 5000 environment configuration performance.

IMPORTANT Use Logix5000™ controllers on DH-485 networks only when you want to add controllers to an existing DH-485 network. For new applications with Logix5000 controllers, we recommend open architecture networks.

You need a 1761-NET-AIC converter for each controller on the DH-485 network. You can have two controllers per one 1761-NET-AIC converter, but you need a different cable for each controller. Connect one controller to port 1 (9-pin connector) and one controller to port 2 (mini-DIN connector).

| To connect to this port | Use this cable |
|--|------------------------------|
| Port 1 DB-9 RS-232, DTE connection | 1747-CP3, 1761-CBL-AC00 |
| Port 2 mini-DIN 8 RS-232 connection | 1761-CBL-AP00, 1761-CBL-PM02 |

Table 25 - Technical Specifications - 1756-DH485 Module

| Attribute | 1756-DH485 |
|---------------------------------|--|
| Communication rate | 19.2 Kbps 9600 Kbps |
| Current draw @ 5.1V DC | 850 mA |
| Current draw @ 24V DC | 1.7 mA |
| Power dissipation | 4.5 W |
| Thermal dissipation | 15.4 BTU/hr |
| Isolation voltage | 50V (continuous), basic insulation type, DH485 A/B to backplane, and DH485 A to DH485 B Type tested at 750V DC for 60 s |
| Slot width | 1 |
| Module location | Chassis |
| Power supply, standard | 1756-PA72/C, 1756-PA75/B, 1756-PB72/C, 1756-PB75/B, 1756-PC75/B, 1756-PH75/B |
| Power supply, redundant | 1756-PA75R, 1756-PB75R, 1756-PSCA2 |
| Ports | 2 DH-485 9-pin, D-shell |
| Wiring category ⁽¹⁾ | 2 - on DH485 ports |
| North American temperature code | T5 |
| Enclosure type rating | None (open-style) |

(1) Use this conductor category information for planning conductor routing as described in the system level installation manual. See the Industrial Automation Wiring and Grounding Guidelines, publication [1770-4.1](#).

Table 26 - Environmental Specifications - 1756-DH485 Module

| Attribute | 1756-DH485 |
|---|--|
| Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | 0...60 °C (32...140 °F) |
| Temperature, surrounding air, max. | 60 °C (140 °F) |
| Temperature, storage IEC 60068-2-1 (Test Ab, Unpackaged Nonoperating Cold) IEC 60068-2-2 (Test Bb, Unpackaged Nonoperating Dry Heat) IEC 60068-2-14 (Test Na, Unpackaged Nonoperating Thermal Shock) | -40...85 °C (-40...185 °F) |
| Relative humidity IEC 60068-2-30 (Test Db, Unpackaged Damp Heat) | 5...95% noncondensing |
| Vibration IEC 60068-2-6 (Test Fc, Operating) | 2 g @ 10...500 Hz |
| Shock, operating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g |
| Shock, nonoperating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 50 g |
| Emissions CISPR 11 (IEC 61000-6-4) | Class A |
| ESD immunity IEC 61000-4-2 | 4 kV contact discharges 8 kV air discharges |
| Radiated RF immunity IEC 61000-4-3 | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM @ 900 MHz 1V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz |
| EFT/B immunity IEC 61000-4-4 | ±2 kV at 5 kHz on communication ports |
| Surge transient immunity IEC 61000-4-5 | ±1 kV line-earth (CM) on communication ports |
| Conducted RF immunity IEC 61000-4-6 | 10V rms with 1 kHz sine-wave 80% AM from 150 kHz...80 MHz |

Table 27 - Certifications - 1756-DH485 Module

| Certification ⁽¹⁾ | 1756-DH485 |
|------------------------------|--|
| c-UL-us | UL Listed for Class I, Division 2 Group A,B,C,D Hazardous Locations, certified for U.S. and Canada. See UL File E194810. |
| CE | European Union 2004/108/IEC EMC Directive, compliant with the following: <ul style="list-style-type: none"> • EN 61326-1; Meas./Control/Lab., Industrial Requirements • EN 61000-6-2; Industrial Immunity • EN 61000-6-4; Industrial Emissions • EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) |
| RCM | Australian Radiocommunications Act, compliant with EN 61000-6-4; Industrial Emissions |
| KC | Korean Registration of Broadcasting and Communications Equipment, compliant with: Article 58-2 of Radio Waves Act, Clause 3 |

(1) When product is marked. See the Product Certification link at <http://www.ab.com> for Declarations of Conformity, Certificates, and other certification details.

Accessories—DH-485 Network

| Cat. No. | Description | Specifications |
|---------------|--|---|
| 1747-CP3 | 9-pin D-shell, straight; 9-pin D-shell, right angle | 3 m (9.8 ft) |
| 1761-CBL-AC00 | 9-pin D-shell, right angle; 9-pin D-shell, right angle | 45 cm (17.7 in.) |
| 1761-CBL-AP00 | 9-pin D-shell, right angle; 9-pin mini-DIN | 45 cm (17.7 in.) |
| 1761-CBL-PM02 | 9-pin D-shell, straight; 8-pin mini-DIN | 2 m (6.5 ft) |
| 1761-NET-AIC | Advanced Interface Converter (AIC+) connects each channel on the 1756-DH485 module to the DH-485 network | 20.4...28.8V DC power source required Typical 120 mA 24V DC current draw |
| 9300-RADKIT | Remote access dial-in kit | 56 Kbps modem connection to devices on a DH+ network, including the following: <ul style="list-style-type: none"> • Preconfigured modem • Communication module • DIN rail mounting hardware • Associated cables |

SynchLink Communication

The SynchLink module provides time synchronization and data broadcasting capabilities for distributed motion and coordinated drive control. The 1756-SYNCH SynchLink module connects a ControlLogix chassis to a SynchLink fiber-optic communication link. The module does the following:

- Coordinates Coordinated System Time across multiple ControlLogix chassis
- Moves a limited amount of data from one chassis to another at a high speed
- Lets one controller consume motion axes data from a controller in another chassis

Table 28 - Technical Specifications - 1756-SYNCH Module

| Attribute | 1756-SYNCH |
|-------------------------|---|
| SynchLink data rate | 5 Mbps |
| Operating wavelength | 650 nm (red) |
| Type of communication | Synchronous |
| Frame period | 50 μ s |
| Frame parameters | 3 Flags - 3 bytes Control field - 1 byte Data field - 24 bytes CRC field - 2 bytes |
| Current draw @ 5.1V DC | 1200 mA |
| Current draw @ 24V DC | 3 mA |
| Power dissipation | 6.2 W |
| Thermal dissipation | 21.2 BTU/hr |
| Slot width | 1 |
| Module location | Chassis-based, any slot |
| Chassis | 1756-A4, 1756-A7, 1756-A10, 1756-A13, 1756-A17 |
| Power supply, standard | 1756-PA72/C, 1756-PA75/B, 1756-PB72/C, 1756-PB75/B, 1756-PC75/B, 1756-PH75/B |
| Power supply, redundant | 1756-PA1756-PA75R, 1756-PB75R, 1756-PSCA2 |

Table 28 - Technical Specifications - 1756-SYNCH Module (Continued)

| Attribute | 1756-SYNCH |
|------------------------------|---------------------------------------|
| Ports | 2 fiber optic |
| Cable fiber type | 200/230 micron HCS (Hard Clad Silica) |
| Cable fiber termination type | Versalink V-System |
| Cable length | 1...300 m (3.28...984.2 ft) |
| North American Temp Code | T4A |
| Enclosure type rating | None (open-style) |

Table 29 - Environmental Specifications - 1756-SYNCH Module

| Attribute | 1756-SYNCH |
|---|---|
| Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | 0...60 °C (32...140 °F) |
| Temperature, surrounding air, max. | 60 °C (140 °F) |
| Temperature, storage IEC 60068-2-1 (Test Ab, Unpackaged Nonoperating Cold) IEC 60068-2-2 (Test Bb, Unpackaged Nonoperating Dry Heat) IEC 60068-2-14 (Test Na, Unpackaged Nonoperating Thermal Shock) | -40...85 °C (-40...185 °F) |
| Relative humidity IEC 60068-2-30 (Test Db, Unpackaged Damp Heat) | 5...95% noncondensing |
| Vibration IEC 60068-2-6 (Test Fc, Operating) | 2 g @ 10...500 Hz |
| Shock, operating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 30 g |
| Shock, nonoperating IEC 60068-2-27 (Test Ea, Unpackaged Shock) | 50 g |
| Emissions CISPR 11 (IEC 61000-6-4) | Class A |
| ESD immunity IEC 61000-4-2 | 6 kV contact discharges 8 kV air discharges |
| Radiated RF immunity IEC 61000-4-3 | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM at 900 MHz 1V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz |

Table 30 - Certifications - 1756-SYNCH Module

| Certification ⁽¹⁾ | 1756-SYNCH |
|------------------------------|---|
| UL | UL Listed Industrial Control Equipment. See UL file E65584 |
| CSA | CSA Certified Process Control Equipment. See CSA File LR54689C CSA Certified Process Control Equipment for Class I, Division 2 Group A,B,C,D Hazardous Locations. See CSA file LR69960C |
| CE | European Union 2004/108/EC EMC Directive, compliant with the following: <ul style="list-style-type: none"> • EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) • EN 61326-1; Meas./Control/Lab., Industrial Requirements • EN 61000-6-2; Industrial Immunity • EN 61000-6-4; Industrial Emissions |
| RCM | Australian Radiocommunications Act, compliant with EN 61000-6-4; Industrial Emissions |
| FM | FM Approved Equipment for use in Class I Division 2 Group A,B,C,D Hazardous Locations |
| KC | Korean Registration of Broadcasting and Communications Equipment, compliant with: Article 58-2 of Radio Waves Act, Clause 3 |

(1) When product is marked. See the Product Certification link at <http://www.ab.com> for Declarations of Conformity, Certificates, and other certification details.

Accessories—SynchLink Network

| Cat. No. | Description |
|------------------|--|
| 1403-CFxxx | Rockwell Automation fiber-optic cable assembly |
| HCP-M0200T V01RK | Lucent Technologies 200 μ m simplex cable |

Time Synchronization

The 1756-TIME module provides accurate time synchronization on different interfaces by using Global Positioning System (GPS) technology. The 1756-TIME module can obtain time from various sources, and provide time synchronization on other devices by acting as a gateway between different time synchronization methods and standards.

Time synchronization is accomplished by using these methods, standards, and protocols:

- The ControlLogix® backplane for Coordinated System Time (CST) and Coordinated Universal Time (UTC) conversion.
- Inter-range Instrumentation Group, code B (IRIG-B) standards.
- Precision Time Protocol (PTP) on Ethernet and the ControlLogix® backplane.
- Network Time Protocol (NTP) on Ethernet.

The 1756-TIME module:

- Provides GPS position in the form of latitude, longitude, and altitude (LLA).
- Provides course and route information in the form of ground speed (knots) with heading in the form of degrees from true north.
- Operates within the ControlLogix platform. All power that is required for the operation of the module is supplied by the ControlLogix backplane.
- The K in the catalog number, 1756-TIMEK, indicates that the module has the conformal coating option.

Table 31 - Technical Specifications - 1756-TIME Module

| Attribute | Description |
|--|--|
| Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | 0...+50 °C (+32...+122 °F) in a Series B Chassis 0...+60 °C (+32...+140 °F) in a Series C Chassis |
| Temperature, surrounding air, max | +50 °C (+122 °F) in a Series B Chassis +60 °C (+140 °F) in a Series C Chassis |
| Temperature, nonoperating IEC 60068-2-1 (Test Ad, Operating Cold) IEC 60068-2-2 (Test Bd, Operating Dry Heat) IEC 60068-2-14 (Test Nb, Operating Thermal Shock) | -40...+85 °C (-40...+185 °F) |
| Relative humidity IEC 60068-2-30 (Test Db, Unpackaged Damp Heat) | 5...95% noncondensing |
| Emissions | IEC 61000-6-4 |
| EDS Immunity IEC 61000-4-2 | 4 kV contact discharges 8 kV air discharges |
| Radiated RF Immunity IEC 61000-4-3 | 10V/m with 1 kHz sine-wave 80% AM from 80...2000 MHz 10V/m with 200 Hz 50% Pulse 100% AM at 900 MHz 10V/m with 200 Hz 50% Pulse 100% AM at 1890 MHz 3V/m with 1 kHz sine-wave 80% AM from 2000...2700 MHz 3V/m with 1 kHz sine-wave 80% AM from 2700...6000 MHz |
| EFT/B Immunity IEC 61000-4-4 | ±2 kV at 5 kHz on signal ports ±2 kV at 5 kHz on communications ports |
| Surge Transient Immunity IEC 61000-4-5 | ±2 kV line-earth(CM) on signal ports no shielded ports - omit from publication ±2 kV line-earth(CM) on communications ports |
| Conducted RF Immunity IEC 61000-4-6 | 10V rms with 1 kHz sine-wave 80% AM from 150 kHz...80 MHz |
| Enclosure type rating | None (open-style) |
| Voltage and current ratings | Backplane: 1.01A @ 5.1V DC, 2.64 mA @ 1.2 V DC |
| Isolation voltage | 30V (continuous), Basic Insulation Type Type tested at 1000V AC for 60 s <ul style="list-style-type: none"> Ethernet Ports to Backplane IRIG-B to Backplane |
| Wire size | Ethernet connections <ul style="list-style-type: none"> RJ45 connector according to IEC 60603-7, 2 or 4 pair Category 5e minimum cable according to TIA 568-B.1 or Category 5 cable according to ISO/IEC 24702. IRIG-B connection <ul style="list-style-type: none"> Type RG58 or equivalent Antenna connection <ul style="list-style-type: none"> Cable assembly, TNC Plug to SMA, ships with product. |
| Wiring Category ⁽¹⁾ | <ul style="list-style-type: none"> 2 - on signal ports 2 - on communications ports |

(1) Use this Conductor Category information for planning conductor routing. See the Industrial Automation Wiring and Grounding Guidelines, publication [1770-4.1](#).

Table 32 - Certifications - 1756-TIME Module

| Certification⁽¹⁾ (when product is marked) | Description |
|---|---|
| c-UL-us | UL Listed Industrial Control Equipment, certified for US and Canada. See UL File E65584. |
| CE | <ul style="list-style-type: none"> • EN 61326-1; Meas./Control/Lab., Industrial Requirements • EN 61000-6-2; Industrial Immunity • EN 61000-6-4; Industrial Emissions • EN 61131-2; Programmable Controllers (Clause 8, Zone A & B) |
| CE | <p>European Union 1999/5/EC R&TTE, compliant with:</p> <ul style="list-style-type: none"> • EN 61010-1; Measurement, Control, and Laboratory Equipment Safety Requirements • EN 61010-2-201; Control Equipment Safety Requirements • EN 300 440-1 V1.6.1; CSE <p>European Union 2011/65/EU RoHS, compliant with:</p> <ul style="list-style-type: none"> • EN 50581; Technical documentation |
| RCM | <p>Australian Radiocommunications Act, compliant with:</p> <ul style="list-style-type: none"> • EN 61000-6-4; Industrial Emissions |
| KC | <p>Korean Registration of Broadcasting and Communications Equipment, compliant with:</p> <ul style="list-style-type: none"> • Article 58-2 of Radio Waves Act, Clause 3 |

(1) See the Product Certification link at www.ab.com for Declarations of Conformity, Certificates, and other certification details.

Notes:

Important User Information

Read this document and the documents listed in the additional resources section about installation, configuration, and operation of this equipment before you install, configure, operate, or maintain this product. Users are required to familiarize themselves with installation and wiring instructions in addition to requirements of all applicable codes, laws, and standards.

Activities including installation, adjustments, putting into service, use, assembly, disassembly, and maintenance are required to be carried out by suitably trained personnel in accordance with applicable code of practice.

If this equipment is used in a manner not specified by the manufacturer, the protection provided by the equipment may be impaired.

In no event will Rockwell Automation, Inc. be responsible or liable for indirect or consequential damages resulting from the use or application of this equipment.

The examples and diagrams in this manual are included solely for illustrative purposes. Because of the many variables and requirements associated with any particular installation, Rockwell Automation, Inc. cannot assume responsibility or liability for actual use based on the examples and diagrams.

No patent liability is assumed by Rockwell Automation, Inc. with respect to use of information, circuits, equipment, or software described in this manual.

Reproduction of the contents of this manual, in whole or in part, without written permission of Rockwell Automation, Inc., is prohibited.

Documentation Feedback

Your comments will help us serve your documentation needs better. If you have any suggestions on how to improve this document, complete this form, publication [RA-DU002](#), available at <http://www.rockwellautomation.com/literature/>.

Rockwell Automation maintains current product environmental information on its website at <http://www.rockwellautomation.com/rockwellautomation/about-us/sustainability-ethics/product-environmental-compliance.page>.

Allen-Bradley, ControlLogix, ControlLogix-XT, Data Highway Plus, DH+, KwikLink, Logix5000, NetLinx, PLC-5, PanelView, Rockwell Automation, Rockwell Software, RSLinx, RSLogix, SLC, Stratix, Stratix 8300, Stratix 5700, Stratix 8000, Stratix 6000, Stratix 2000, Studio 5000, and SynchLink are trademarks of Rockwell Automation, Inc.

Trademarks not belonging to Rockwell Automation are property of their respective companies.

Rockwell Otomasyon Ticaret A.Ş., Kar Plaza İş Merkezi E Blok Kat:6 34752 İçerenköy, İstanbul, Tel: +90 (216) 5698400

www.rockwellautomation.com

Power, Control and Information Solutions Headquarters

Americas: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444

Europe/Middle East/Africa: Rockwell Automation NV, Pegasus Park, De Kleetlaan 12a, 1831 Diegem, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640

Asia Pacific: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846

Publication 1756-TD003J-EN-E - April 2017

Supersedes Publication 1756-TD003I-EN-E - January 2016

Copyright © 2017 Rockwell Automation, Inc. All rights reserved. Printed in the U.S.A.